

19" ASSEMBLY KIT M6



For standard grounding use a grounding nut and washer on at least one attachment point.

When 19" assembly kit is used with conductive 19" panel mount, grounding cage nuts are not needed.

CERTIFICATIONS



CARATTERISTICHE

Assembly kits for assembly of 19" components into a cabinet

For mounting of front panels, distribution fields or other components on the frame, slide mounts or depth members with square cut-outs

SPECIFICHE

Table 1/2

Codice a catalogo	Tipo	Accessory Type	Product Type	Works With	Quantità per confezione	Finitura
21120-196	Mounting Kit	Mounting hardware	Assembly Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	4	Zinc Plated
21120-213	Mounting Kit	Mounting hardware	Assembly Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	4	Zinc Plated

Codice a catalogo	Tipo	Accessory Type	ProductType	Works With	Quantità per confezione	Finitura
21100-435	Mounting Kit	Mounting hardware	Assembly Kit	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	8	Zinc Plated
21120-199	Mounting Kit	Mounting hardware	Assembly Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	100	Zinc Plated
21120-197	Mounting Kit	Mounting hardware	Assembly Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	32	Zinc Plated
21120-198	Mounting Kit	Mounting hardware	Assembly Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	50	Zinc Plated
21101-809	Mounting Kit	Mounting hardware	Assembly Kit	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	50	Zinc Plated
21101-810	Mounting Kit	Mounting hardware	Assembly Kit	19" Cases, 19" Wallmount, 19" Indoor Cabinets, 19" Outdoor Cabinets	100	Zinc Plated
21120-215	Mounting Kit	Mounting hardware	Assembly Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	32	Zinc Plated
21120-214	Mounting Kit	Mounting hardware	Assembly Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	50	Zinc Plated
21120-216	Mounting Kit	Mounting hardware	Assembly Kit	Front Panels, Eurorack, Novastar, Varistar, Varistar CP	100	Zinc Plated

Table 2/2

Codice a catalogo	Materiale	Length	Thread Size	Certifications
21120-196	Steel	16mm	M6	
21120-213	Steel		M6	
21100-435	Steel, ABS		M6	RoHS
21120-199	Steel	13mm	M6	
21120-197	Steel	16mm	M6	
21120-198	Steel	16mm	M6	
21101-809	Steel, ABS		M6	RoHS
21101-810	Steel, ABS		M6	RoHS
21120-215	Steel		M6	
21120-214	Steel		M6	
21120-216	Steel		M6	

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER