

SHELF FOR AIR CIRCUIT-BREAKERS (ACB) | ALIMENTAZIONE E DISTRIBUZIONE, MSCC



The galvanised steel shelf, MSCC, covers a partial depth of an enclosure and is ideal for equipment requiring strong fixation, such as heavy air circuit breakers. It leaves the rear of the enclosure accessible for easy installation and wiring.

CARATTERISTICHE

Descrizione: Shelf to mount air circuit-breakers, fixed or withdrawable version and MCCB's version in cassette. The shelf has ventilation slots to allow air circulation in the section. It can be mounted only if we have internal side panels MSPSxx06 in both sides. Adjustable height position in steps of 25mm. It can not be used with the front covers system, if it is necessary to increase the internal segregation or limit the access, we recommend to use top and bottom shelf and 3 partial doors to separate the incoming, ACB and outgoing subsections.

Materiale: 2 mm galvanised steel.

Fornitura: 1 piece with mounting material.

In order to mount the shelf, internal side panels (MSPS), are required

Shelf to mount air circuit-breakers, fixed or withdrawable version and MCCB's version in cassette

The shelf has ventilation slots to allow air circulation in the section

It can be mounted only if we have internal side panels MSPSxx06 in both sides

Adjustable height position in steps of 25mm

It can not be used with the front covers system, if it is necessary to increase the internal segregation or limit the access, we recommend to use top and bottom shelf and 3 partial doors to separate the incoming, ACB and outgoing subsections

Includes mounting hardware

Comprende la ferramenta necessaria per il montaggio

SPECIFICHE

- Spessore:

2mm
- Materiale:

Mild Steel
- Finish:

Plated

Table 1/1						
Codice a catalogo	Altezza	Larghezza	Profondità	Larghezza piastra di montaggio	Profondità di montaggio massima	Materiale della recinzione
MSCC0606	78mm	600mm	600mm	504mm	283mm	Mild Steel
MSCC0806	78mm	800mm	600mm	704mm	283mm	Mild Steel
MSCC1006	78mm	1000mm	600mm	904mm	283mm	Mild Steel

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



nVent.com

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF

TRACER