


U-PROFILE FRONT PANEL, SHIELDABLE, D-SUB CUTOUTS



U-profile front panel with cutout for D-Sub connectors.
Shieldable for textile EMC gasket.

CERTIFICATIONS



FEATURES

U-profile, front panel, Aluminum, 2.5 mm, front anodized, rear conductive

For EMC textile gasket

SPECIFICATIONS

Table 1/3						
Numero catalogo	EMC Gasket Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30849-749	Textile	No	Anodized	Conductive	No (Retrofittable)	4 HP
30849-750	Textile	No	Anodized	Conductive	No (Retrofittable)	4 HP

Numero catalogo	EMC Gasket Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30849-751	Textile	No	Anodized	Conductive	No (Retrofittable)	4 HP
30849-752	Textile	No	Anodized	Conductive	No (Retrofittable)	4 HP
30849-753	Textile	No	Anodized	Conductive	No (Retrofittable)	4 HP
30849-754	Textile	No	Anodized	Conductive	No (Retrofittable)	4 HP
30849-755	Textile	No	Anodized	Conductive	No (Retrofittable)	4 HP

Table 2/3						
Numero catalogo	Package Quantity	Altezza	Product Type	Tipo	Rack Height	Larghezza
30849-749	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30849-750	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30849-751	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30849-752	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30849-753	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30849-754	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30849-755	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm

Table 3/3			
Numero catalogo	È conforme a	Montaggio	Materiale
30849-749	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio
30849-750	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio
30849-751	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio
30849-752	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio
30849-753	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio

Numero catalogo	È conforme a	Montaggio	Materiale
30849-754	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio
30849-755	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Alluminio

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please order textile EMC gasket separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER