


SOCKET STRIP, UTE



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with UTE outlets.

CERTIFICATIONS



CARATTERISTICHE

230 V, 16 A

In accordance with NFC 61-303

Socket strip with UTE sockets

Mounting height 1 U

Horizontal or vertical mounting

Connecting cable 2 m, with SCHUKO/UTE plug

Socket strips can be rotated through all four directions (in 90° increments) during installation

SPECIFICHE

Table 1/2

Codice a catalogo	Product Type	Tipo di presa	Socket Quantity	Switched Outlets	Colore	Tensione AC
60110-220	Socket Strip	UTE	4	No	Grey	230V
60110-221	Socket Strip	UTE	9	No	Grey	230V
60110-222	Socket Strip	UTE	12	No	Grey	230V

Codice a catalogo	ProductType	Tipo di presa	Socket Quantity	Switched Outlets	Colore	Tensione AC
60110-223	Socket Strip	UTE	15	No	Grey	230V
60110-224	Socket Strip	UTE	19	No	Grey	230V
60110-225	Socket Strip	UTE	8	Yes	Grey	230V
60110-226	Socket Strip	UTE	12	Yes	Grey	230V
60110-227	Socket Strip	UTE	8	No	Grey	230V
60110-228	Socket Strip	UTE	6	No	Grey	230V
60110-229	Socket Strip	UTE	7	No	Grey	230V
60110-230	Socket Strip	UTE	6	No	Grey	230V
60110-231	Socket Strip	UTE	6	No	Grey	230V
60110-267	Socket Strip	UTE	6	No	Grey	230V

Table 2/2						
Codice a catalogo	Function	Length	Profondità	Finitura	Materiale	Quantità per confezione
60110-220		210mm	44mm	Anodized	Aluminum, Polyamide	1
60110-221		438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-222		947.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-223		1202mm	44mm	Anodized	Aluminum, Polyamide	1
60110-224		1753mm	44mm	Anodized	Aluminum, Polyamide	1
60110-225		438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-226		947.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-227	Transient Protection	438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-228	Overcurrent Protection	438.5mm	75mm	Anodized	Aluminum, Polyamide	1
60110-229	Mains Suppression Filter	438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-230	Fault Current Protection	438.5mm	88mm	Anodized	Aluminum, Polyamide	1

Codice a catalogo	Function	Length	Profondità	Finitura	Materiale	Quantità per confezione
60110-231	Fault Current Protection, Overcurrent Protection	438.5mm	88mm	Anodized	Aluminum, Polyamide	1
60110-267	Transient Protection, Mains Suppression Filter	438.5mm	44mm	Anodized	Aluminum, Polyamide	1

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER