


FRONT HANDLE ONE-PIECE, WIDTH 12,2 MM



The handle can be assembled to a subrack or 19" front panel. Available with clear or black anodized surface. Handles will be bolted from the rear side.

CERTIFICATIONS



FEATURES

Static load-carrying capacity 30 kg/pair

Bolted from rear

SPECIFICATIONS

Table 1/2

Número catalogo	Handle Type	Package Quantity	Tipo	Product Type	Product Family	Works With
10501-116	Dritto	1	Straight version	Handle	EuropacPRO	Subracks
10501-004	Dritto	1	Straight version	Handle	EuropacPRO	Subracks
10501-020	Angled Handle	1	Angled version	Handle	EuropacPRO	Subracks
10501-026	Dritto	1	Straight version	Handle	EuropacPRO	Subracks
10501-005	Dritto	1	Straight version	Handle	EuropacPRO	Subracks
10501-006	Dritto	1	Straight version	Handle	EuropacPRO	Subracks
10501-007	Dritto	1	Straight version	Handle	EuropacPRO	Subracks
10501-022	Angled Handle	1	Angled version	Handle	EuropacPRO	Subracks

Numero catalogo	Handle Type	Package Quantity	Tipo	ProductType	Product Family	Works With
10501-029	Dritto	1	Straight version	Handle	EuropacPRO	Subracks
10501-008	Dritto	1	Straight version	Handle	EuropacPRO	Subracks
10501-016	Dritto	1	Straight version	Handle	EuropacPRO	Subracks
10501-021	Angled Handle	1	Angled version	Handle	EuropacPRO	Subracks
10501-018	Dritto	1	Straight version	Handle	EuropacPRO	Subracks
10501-025	Dritto	1	Straight version	Handle	EuropacPRO	Subracks
10501-027	Dritto	1	Straight version	Handle	EuropacPRO	Subracks
10501-028	Dritto	1	Straight version	Handle	EuropacPRO	Subracks

Table 2/2					
Numero catalogo	Rack Height	Colore	Materiale	Accessory Type	Coppia
10501-116	1 U	Silver	Alluminio	Front panel	
10501-004	2 U	Silver	Alluminio	Front panel	
10501-020	3 U	Silver	Alluminio		2.4 N·m
10501-026	3 U	Nero	Alluminio	Front panel	2.4 N·m
10501-005	3 U	Silver	Alluminio		2.4 N·m
10501-006	4 U	Silver	Alluminio	Front panel	
10501-007	5 U	Silver	Alluminio	Front panel	
10501-022	6 U	Silver	Alluminio		2.4 N·m
10501-029	6 U	Nero	Alluminio	Front panel	2.4 N·m
10501-008	6 U	Silver	Alluminio		2.4 N·m
10501-016	2 U	Silver	Alluminio	Front panel	
10501-021	4 U	Silver	Alluminio		2.4 N·m
10501-018	4 U	Silver	Alluminio	Front panel	2.4 N·m
10501-025	2 U	Nero	Alluminio	Front panel	
10501-027	4 U	Nero	Alluminio	Front panel	
10501-028	5 U	Nero	Alluminio	Front panel	

ADDITIONAL PRODUCT DETAILS

Please order assembly part kit separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

AVVERTENZA

AVVERTENZA: i prodotti nVent devono essere installati e usati solo secondo le indicazioni riportate nei fogli delle istruzioni del prodotto nVent e nei materiali di formazione. I fogli di istruzioni sono disponibili sul sito www.nvent.com e presso il vostro rappresentante locale dell'assistenza clienti di nVent. Un'installazione scorretta, l'uso improprio, l'applicazione errata o altre inosservanze delle istruzioni e delle avvertenze di nVent possono causare un malfunzionamento del prodotto, danni alle proprietà, lesioni corporee gravi e morte e/o l'annullamento della garanzia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER