


FRONT HANDLE ONE-PIECE, WIDTH 12,2 MM



The handle can be assembled to a subrack or 19" front panel. Available with clear or black anodized surface. Handles will be bolted from the rear side.

CERTIFICATIONS



FEATURES

Static load-carrying capacity 30 kg/pair

Bolted from rear

SPECIFICATIONS

Table 1/2

Catalogusnummer	Handle Type	Package Quantity	Type	Product Type	Product Family	Works With
10501-116	Recht	1	Straight version	Handle	EuropacPRO	Subracks
10501-004	Recht	1	Straight version	Handle	EuropacPRO	Subracks
10501-020	Angled Handle	1	Angled version	Handle	EuropacPRO	Subracks
10501-026	Recht	1	Straight version	Handle	EuropacPRO	Subracks
10501-005	Recht	1	Straight version	Handle	EuropacPRO	Subracks
10501-006	Recht	1	Straight version	Handle	EuropacPRO	Subracks
10501-007	Recht	1	Straight version	Handle	EuropacPRO	Subracks
10501-022	Angled Handle	1	Angled version	Handle	EuropacPRO	Subracks

Catalogusnummer	Handle Type	Package Quantity	Type	ProductType	Product Family	Works With
10501-029	Recht	1	Straight version	Handle	EuropacPRO	Subracks
10501-008	Recht	1	Straight version	Handle	EuropacPRO	Subracks
10501-016	Recht	1	Straight version	Handle	EuropacPRO	Subracks
10501-021	Angled Handle	1	Angled version	Handle	EuropacPRO	Subracks
10501-018	Recht	1	Straight version	Handle	EuropacPRO	Subracks
10501-025	Recht	1	Straight version	Handle	EuropacPRO	Subracks
10501-027	Recht	1	Straight version	Handle	EuropacPRO	Subracks
10501-028	Recht	1	Straight version	Handle	EuropacPRO	Subracks

Table 2/2					
Catalogusnummer	Rack Height	Kleur	Materiaal	Accessory Type	Aandraaimoment
10501-116	1 U	Silver	Aluminium	Front panel	
10501-004	2 U	Silver	Aluminium	Front panel	
10501-020	3 U	Silver	Aluminium		2.4 N·m
10501-026	3 U	Zwart	Aluminium	Front panel	2.4 N·m
10501-005	3 U	Silver	Aluminium		2.4 N·m
10501-006	4 U	Silver	Aluminium	Front panel	
10501-007	5 U	Silver	Aluminium	Front panel	
10501-022	6 U	Silver	Aluminium		2.4 N·m
10501-029	6 U	Zwart	Aluminium	Front panel	2.4 N·m
10501-008	6 U	Silver	Aluminium		2.4 N·m
10501-016	2 U	Silver	Aluminium	Front panel	
10501-021	4 U	Silver	Aluminium		2.4 N·m
10501-018	4 U	Silver	Aluminium	Front panel	2.4 N·m
10501-025	2 U	Zwart	Aluminium	Front panel	
10501-027	4 U	Zwart	Aluminium	Front panel	
10501-028	5 U	Zwart	Aluminium	Front panel	

ADDITIONAL PRODUCT DETAILS

Please order assembly part kit separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER