

MULTI ATTACHMENT



CERTIFICATIONS



KENMERKEN

Disperses load over two anchors

Minimizes the number of installed braces needed for concrete and wood structures

Ideal for deck installations

Use for both lateral and longitudinal sway brace applications

Meets NFPA®-13 requirements for seismic sway bracing

Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing

SPECIFICATIES

Afwerking: Electrogalvanized

Materiaal: Steel

Table 1/2

Catalogusnummer	Article Number	Formaat gat 1 (HS1)	Formaat gat 2 (HS2)	A	C	B
CSBMA050050EG	404371	14mm	14mm	304.8mm	63.5mm	63.5mm

Catalogusnummer	Article Number	Formaat gat 1 (HS1)	Formaat gat 2 (HS2)	A	C	B
CSBMA050075EG	404372	20mm	14mm	304.8mm	63.5mm	63.5mm

Table 2/2		
Catalogusnummer	Article Number	D
CSBMA050050EG	404371	228.6mm
CSBMA050075EG	404372	228.6mm

ADDITIONAL PRODUCT DETAILS


Mount to structure using holes indicated in HS1.

Structure Attachment and Brace Member are not included.

Draagvermogen naar UL			
Onderdeelnummer	Constructiebevestiging	Diagonaalsteun	Toegestane belasting
CSBMA050050	CSBU1	DN25 - DN50 Sch. 40 NPS	3025 N
	CSBUNIV050	DN25 - DN50 Sch. 40 NPS	3025 N
	CSBURC12	CSB12CBL	1859 N
		CSB18CBL	3434 N
		CSB36CBL	4893 N
	CSBURC12	CSB12CBL	1859 N
		CSB18CBL	3434 N
		CSB36CBL	5783 N
CSBMA050075	CSBU1	DN25 - DN50 Sch. 40 NPS	3025 N
	CSBUNIV050	DN25 - DN50 Sch. 40 NPS	3025 N
	CSBURC12	CSB12CBL	1859 N
		CSB18CBL	3434 N
		CSB36CBL	4893 N
	CSBURC12	CSB12CBL	1859 N
		CSB18CBL	3434 N
		CSB36CBL	5783 N

Laadvermogen volgens FM				
Onderdeelnummer	Horizontale capaciteit per installatiehoek van het verticale vlak			
	30° - 44°	45° - 59°	60° - 74°	75° - 90°
CSBMA050050EG	14,630 N	20,100 N	24,640 N	27,570 N
CSBMA050075EG	14,630 N	20,100 N	24,640 N	27,570 N

DIAGRAMS



WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER