


ASSEMBLY PARTS FOR RUGGED COMPONENTS



Assembly parts with thread-locking compound for rugged Side Panel, horizontal rail, cover plates, rear angle.

CERTIFICATIONS



FEATURES

Screws for the following fixings: Rugged side panel - horizontal rail, Rugged side panel - cover plate, Rugged side panel - rear angle

SPECIFICATIONS

Table 1/2						
Catalogusnummer	Formaat draad	Package Quantity	Product Type	Product Family	Works With	Type
24566-105	M4	100	Assembly Kit	EuropacPRO	Subracks	Countersunk Screw
24566-104	M4	100	Assembly Kit	EuropacPRO	Subracks	Panhead Screw
24566-103	M4	100	Assembly Kit	EuropacPRO	Subracks	Panhead Screw
24566-106	M4	100	Assembly Kit	EuropacPRO	Subracks	Countersunk Screw
24566-101	M4	100	Assembly Kit	EuropacPRO	Subracks	Countersunk Screw
24566-102	M4	100	Assembly Kit	EuropacPRO	Subracks	Panhead Screw
24566-100	M4	100	Assembly Kit	EuropacPRO	Subracks	Countersunk Screw

Catalogusnummer	Formaat draad	Package Quantity	ProductType	Product Family	Works With	Type
24560-140		100	Assembly Kit	EuropacPRO	Subracks	Square Nut

Table 2/2

Catalogusnummer	Materiaal	Lengte
24566-105	Roestvrij staal	7 mm
24566-104	Roestvrij staal	8 mm
24566-103	Roestvrij staal	10 mm
24566-106	Roestvrij staal	10 mm
24566-101	Roestvrij staal	14 mm
24566-102	Roestvrij staal	14 mm
24566-100	Roestvrij staal	18 mm
24560-140	Roestvrij staal	

WAARSCHUWING

Producten van nVent moeten worden geïnstalleerd en gebruikt op de manier zoals is aangegeven in de nVent productinformatiebladen en trainingsmaterialen. U kunt de productinformatiebladen downloaden van www.nvent.com of opvragen bij uw nVent-klantenservice. Door onjuist installeren, verkeerd gebruik, verkeerde toepassing of enige andere handeling in strijd met de instructies en waarschuwingen van nVent kan het product mogelijk niet correct werken, ernstig of fataal letsel en materiële schade veroorzaken en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER