


CABLE TO REBAR, RD, 13 MM, #4, 4/0 CONCENTRIC, WEAR PLATES

NUMER KATALOGOWY

RDM522QW



nVent ERICO Cadweld graphite molds are designed and engineered for thousands of connection styles and conductor combinations.

CERTIFICATIONS



KENMERKEN

Forms a permanent, low resistance connection

Provides a molecular bond

nVent ERICO Cadweld Exothermic Connections are rated with the same current capacity as the conductor

Portable installation equipment with no external source of power required

Installers can be easily trained to make nVent ERICO Cadweld Exothermic Connections

Connections can be visually inspected

ATRYBUTY PRODUKTU

Rodzina form: RD Mold Family

Rozmiar pręta zbrojeniowego, metryczny: 13mm

Rozmiar pręta zbrojeniowego, USA: #4

Rozmiar przewodnika: 4/0 Concentric

Średnica zewnętrzna przewodu, nominalna: 13.41mm

Mold Split: Vertical

Dzielony tygiel: No

Płyty ścieralne: Yes

Number of Wear Plate Sets: 2

Tylko forma: No

Materiał spawalniczy: 150 or 150PLUSF20, Sold Separately

Podkładka: B141A, Sold Separately

Klucz cenowy: M

Łatwość użytkowania: Preferred

ADDITIONAL PRODUCT DETAILS

For applications such as computer room, tunnel or other low-ventilation areas, specify a smokeless nVent ERICO Cadweld Exolon mold. Add an XL prefix to the standard mold part number when ordering (for example, a TAC2Q2Q becomes XLTAC2Q2Q). Similarly, nVent ERICO Cadweld Exolon welding material is also designated by the XL prefix (for example, 150 becomes XL150).


A gap between conductors may be required. See mold tag for more information.

Rebar material characteristics and location of weld must be considered when selecting connections to rebar.

XX-X-XX-XX-L-M-W		
XX	Mold Family	
X	Price Key	
XX	Rebar Code	
XX	Conductor Code	
L*	Split Crucible	Crucible section is split on molds designed with horizontal opening for easier cleaning
M*	Mold Only	
W*	Wear Plates	Reduce mechanical abrasion of molds at cable entry points

* Empty if none

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER