


FRONT HANDLE ONE-PIECE, WIDTH 12,2 MM



The handle can be assembled to a subrack or 19" front panel. Available with clear or black anodized surface. Handles will be bolted from the rear side.

CERTIFICATIONS



FEATURES

Static load-carrying capacity 30 kg/pair

Bolted from rear

SPECIFICATIONS

Table 1/2

Katalognummer	Handle Type	Package Quantity	Type	Product Type	Product Family	Fungerer med
10501-116	Rett	1	Straight version	Handle	EuropacPRO	Subracks
10501-004	Rett	1	Straight version	Handle	EuropacPRO	Subracks
10501-020	Angled Handle	1	Angled version	Handle	EuropacPRO	Subracks
10501-026	Rett	1	Straight version	Handle	EuropacPRO	Subracks
10501-005	Rett	1	Straight version	Handle	EuropacPRO	Subracks
10501-006	Rett	1	Straight version	Handle	EuropacPRO	Subracks
10501-007	Rett	1	Straight version	Handle	EuropacPRO	Subracks
10501-022	Angled Handle	1	Angled version	Handle	EuropacPRO	Subracks

Katalognummer	Handle Type	Package Quantity	Type	ProductType	Product Family	Fungerer med
10501-029	Rett	1	Straight version	Handle	EuropacPRO	Subracks
10501-008	Rett	1	Straight version	Handle	EuropacPRO	Subracks
10501-016	Rett	1	Straight version	Handle	EuropacPRO	Subracks
10501-021	Angled Handle	1	Angled version	Handle	EuropacPRO	Subracks
10501-018	Rett	1	Straight version	Handle	EuropacPRO	Subracks
10501-025	Rett	1	Straight version	Handle	EuropacPRO	Subracks
10501-027	Rett	1	Straight version	Handle	EuropacPRO	Subracks
10501-028	Rett	1	Straight version	Handle	EuropacPRO	Subracks

Table 2/2					
Katalognummer	Rack Height	Farge	Materiell	Tilbehørstype	Dreiemoment
10501-116	1 U	Silver	Aluminium	Front panel	
10501-004	2 U	Silver	Aluminium	Front panel	
10501-020	3 U	Silver	Aluminium		2.4 N·m
10501-026	3 U	Sort	Aluminium	Front panel	2.4 N·m
10501-005	3 U	Silver	Aluminium		2.4 N·m
10501-006	4 U	Silver	Aluminium	Front panel	
10501-007	5 U	Silver	Aluminium	Front panel	
10501-022	6 U	Silver	Aluminium		2.4 N·m
10501-029	6 U	Sort	Aluminium	Front panel	2.4 N·m
10501-008	6 U	Silver	Aluminium		2.4 N·m
10501-016	2 U	Silver	Aluminium	Front panel	
10501-021	4 U	Silver	Aluminium		2.4 N·m
10501-018	4 U	Silver	Aluminium	Front panel	2.4 N·m
10501-025	2 U	Sort	Aluminium	Front panel	
10501-027	4 U	Sort	Aluminium	Front panel	
10501-028	5 U	Sort	Aluminium	Front panel	

ADDITIONAL PRODUCT DETAILS

Please order assembly part kit separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlatelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER