


FRONT HANDLE ONE-PIECE, WIDTH 12,2 MM



The handle can be assembled to a subrack or 19" front panel. Available with clear or black anodized surface. Handles will be bolted from the rear side.

CERTIFICATIONS



CARACTERÍSTICAS

Static load-carrying capacity 30 kg/pair

Bolted from rear

SPECIFICATIONS

Table 1/2

Número do catálogo	Handle Type	Package Quantity	Tipo	Product Type	Product Family	Works With
10501-116	Reto	1	Straight version	Maçaneta	EuropacPRO	Subracks
10501-004	Reto	1	Straight version	Maçaneta	EuropacPRO	Subracks
10501-020	Angled Handle	1	Angled version	Maçaneta	EuropacPRO	Subracks
10501-026	Reto	1	Straight version	Maçaneta	EuropacPRO	Subracks
10501-005	Reto	1	Straight version	Maçaneta	EuropacPRO	Subracks
10501-006	Reto	1	Straight version	Maçaneta	EuropacPRO	Subracks
10501-007	Reto	1	Straight version	Maçaneta	EuropacPRO	Subracks
10501-022	Angled Handle	1	Angled version	Maçaneta	EuropacPRO	Subracks

Número do catálogo	Handle Type	Package Quantity	Tipo	ProductType	Product Family	Works With
10501-029	Reto	1	Straight version	Maçaneta	EuropacPRO	Subracks
10501-008	Reto	1	Straight version	Maçaneta	EuropacPRO	Subracks
10501-016	Reto	1	Straight version	Maçaneta	EuropacPRO	Subracks
10501-021	Angled Handle	1	Angled version	Maçaneta	EuropacPRO	Subracks
10501-018	Reto	1	Straight version	Maçaneta	EuropacPRO	Subracks
10501-025	Reto	1	Straight version	Maçaneta	EuropacPRO	Subracks
10501-027	Reto	1	Straight version	Maçaneta	EuropacPRO	Subracks
10501-028	Reto	1	Straight version	Maçaneta	EuropacPRO	Subracks

Table 2/2					
Número do catálogo	Rack Height	Cor	Material	Accessory Type	Torque
10501-116	1 U	Silver	Alumínio	Front panel	
10501-004	2 U	Silver	Alumínio	Front panel	
10501-020	3 U	Silver	Alumínio		2.4 N·m
10501-026	3 U	Preto	Alumínio	Front panel	2.4 N·m
10501-005	3 U	Silver	Alumínio		2.4 N·m
10501-006	4 U	Silver	Alumínio	Front panel	
10501-007	5 U	Silver	Alumínio	Front panel	
10501-022	6 U	Silver	Alumínio		2.4 N·m
10501-029	6 U	Preto	Alumínio	Front panel	2.4 N·m
10501-008	6 U	Silver	Alumínio		2.4 N·m
10501-016	2 U	Silver	Alumínio	Front panel	
10501-021	4 U	Silver	Alumínio		2.4 N·m
10501-018	4 U	Silver	Alumínio	Front panel	2.4 N·m
10501-025	2 U	Preto	Alumínio	Front panel	
10501-027	4 U	Preto	Alumínio	Front panel	
10501-028	5 U	Preto	Alumínio	Front panel	

ADDITIONAL PRODUCT DETAILS

Please order assembly part kit separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER