


ASSEMBLY PARTS FOR RUGGED COMPONENTS



Assembly parts with thread-locking compound for rugged Side Panel, horizontal rail, cover plates, rear angle.

CERTIFICATIONS



FEATURES

Screws for the following fixings: Rugged side panel - horizontal rail, Rugged side panel - cover plate, Rugged side panel - rear angle

SPECIFICATIONS

Table 1/2						
Numer katalogowy	Rozmiar gwintu	Package Quantity	Product Type	Product Family	Works With	Typ
24566-105	M4	100	Assembly Kit	EuropacPRO	Subracks	Countersunk Screw
24566-104	M4	100	Assembly Kit	EuropacPRO	Subracks	Panhead Screw
24566-103	M4	100	Assembly Kit	EuropacPRO	Subracks	Panhead Screw
24566-106	M4	100	Assembly Kit	EuropacPRO	Subracks	Countersunk Screw
24566-101	M4	100	Assembly Kit	EuropacPRO	Subracks	Countersunk Screw
24566-102	M4	100	Assembly Kit	EuropacPRO	Subracks	Panhead Screw
24566-100	M4	100	Assembly Kit	EuropacPRO	Subracks	Countersunk Screw

Numer katalogowy	Rozmiar gwintu	Package Quantity	ProductType	Product Family	Works With	Typ
24560-140		100	Assembly Kit	EuropacPRO	Subracks	Square Nut

Table 2/2

Numer katalogowy	Materiał	Długość
24566-105	Stal nierdzewna	7 mm
24566-104	Stal nierdzewna	8 mm
24566-103	Stal nierdzewna	10 mm
24566-106	Stal nierdzewna	10 mm
24566-101	Stal nierdzewna	14 mm
24566-102	Stal nierdzewna	14 mm
24566-100	Stal nierdzewna	18 mm
24560-140	Stal nierdzewna	

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER