



High Performance nVent CADDY CAT HP J-Hook System

Retainer Installation



Part Number	Article Number	Description
CAT32HP	181062	2" [50.8mm] J-Hook
CAT32HPBA	181115	
CAT32HPBU	181112	
CAT32HPGR	181116	
CAT32HPRD	181111	
CAT32HPWH	181113	
CAT32HPYL	181114	
CAT32HPOR	181117	

Working load for all sizes
(3:1 safety factor): 60lbs [276N]

J-Hook color code: CATXXHPXX

J-Hook size = (16)
(21)
(32)
(48)
(64)

J-Hook color
(Optional)
Blank = Pre-Galvanized Finish
(BA) = Black, (BU) = Blue
(GR) = Green, (RD) = Red
(WH) = White, (YL) = Yellow
(OR) = Orange

WARNING:

- nVent products shall be installed and used only as indicated in nVent product instruction sheets and training materials. Instruction sheets are available at www.nVent.com and from your nVent customer service representative.
- nVent products must never be used for a purpose other than the purpose for which they were designed or in a manner that exceeds specified load ratings.
- All instructions must be **completely** followed to ensure proper and safe installation and performance.
- Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and/or death, and void your warranty.
- Products that are manufactured using spring steel components shall be used only in a non-corrosive indoor environment.
- All pipe supports, hangers, intermediate components and structural attachments must **ONLY** be used as described herein and are **NEVER** to be used for any other purpose.

NOTE: All load ratings are for static conditions and do not account for dynamic loading such as wind, water or seismic loads, unless otherwise noted.

The customer is responsible for:

- Conformance to all governing codes.
- The integrity of structures to which the products are attached, including their capability of safely accepting the loads imposed, as evaluated by a qualified engineer.
- Using appropriate industry standard hardware as noted above.

SAFETY INSTRUCTIONS:

All governing codes and regulations and those required by the job site must be observed. Always use appropriate safety equipment such as eye protection, hard hat, and gloves as appropriate to the application.

nVent, nVent CADDY, nVent ERICO Cadweld, nVent ERICO Critec, nVent ERICO, nVent ERIFLEX, and nVent LENTON are owned by nVent or its global affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without prior notice.

TECHNICAL SUPPORT:
www.nVent.com


CFS649_A

1 OF 2


Downloaded by: - 2023-09-28 10:47 © 2022 nVent All Rights Reserved



Wall/General Use



Ceiling Mount



Threaded Rod Mount

