

1 HOLE OFFSET LUG



DESIGN

Provides an efficient bolting surface for grounding and power applications

Electrolytic grade copper

For use with nVent ERICO Cadweld type LA connections only

SPECIFIKATIONER

Finish: Tinned

Table 1/3

Katalognummer	Article Number	Material	Type	Höjd (H)	Bredd (W)	Tjocklek (T)
B101CEOL		Copper	NEMA®	15.88mm	25.4mm	3.18mm
KOF103	183200	Copper	Non-NEMA®	13mm	24.99mm	3mm
B101DEOL		Copper	NEMA®	17.53mm	25.4mm	4.76mm
B305SS		Stainless Steel 304 (EN 1.4301)	Non-NEMA®	20.07mm	29.97mm	5.08mm
B305TC		Copper	Non-NEMA®	20mm	30mm	5mm
B101EEOL		Copper	NEMA®	19.05mm	25.4mm	6.35mm

Table 2/3

Katalognummer	Article Number	Längd (L)	C	B	A	Vinkel (a)
B101CEOL		63.5mm	22.23mm	25.4mm	12.7mm	45°

Katalognummer	Article Number	Längd (L)	C	B	A	Vinkel (a)
KOF103	183200	55mm	25mm	20mm	10mm	45°
B101DEOL		68.33mm	22.23mm	28.58mm	14.3mm	45°
B305SS		91.44mm	39.88mm	33.78mm	15mm	45°
B305TC		91.4mm	39.88mm	33.78mm	15mm	45°
B101EEOL		76.2mm	26.92mm	32.54mm	15.9mm	45°


Table 3/3

Katalognummer	Article Number	Håldimension (HS)	IP-klass
B101CEOL		11.11mm	80.63mm ²
KOF103	183200	8.5mm	74.9mm ²
B101DEOL		14.29mm	120.94mm ²
B305SS		17mm	152.23mm ²
B305TC		17mm	152.23mm ²
B101EEOL		14.29mm	161.26mm ²

ADDITIONAL PRODUCT DETAILS

For sizes not listed, contact us.

DIAGRAMS



VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER