


FRONT PANEL EMC TEXTILE SHIELDING KIT, -40 UP TO +85°C



The textile EMC gaskets are inserted into a slot on the right hand side of the U-shaped front panels. The gaskets are glued to the front panel. For an expanded temperature range up to +85°C.

CERTIFICATIONS



FEATURES

Textile EMC gasket is affixed laterally on the front panel or in the groove of the right-hand profile as appropriate.

Profile seal is bonded onto the contact surface of the 19" bracket or of the rear angle and sets up the conductive connection to the U-shaped front panels

Temperature range -40 °C ... +85 °C

SPECIFICATIONS

Table 1/1

Katalognummer	Package Quantity	Product Type	Product Family	Fungerar med	Rack Height
21102-857	10	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	2 U

Katalognummer	Package Quantity	Product Type	Product Family	Fungerar med	Rack Height
21102-853	10	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	3 U
21102-854	100	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	3 U
21102-858	10	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	4 U
21102-978	10	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	5 U
21102-855	10	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	6 U
21102-856	100	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	6 U
21102-859	10	Shielding Kit	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Subracks, Cases, Front Panels	9 U

ADDITIONAL PRODUCT DETAILS

EMC gaskets (textile) are required for shielding the front panels.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER