


FRONT HANDLE ONE-PIECE, WIDTH 12,2 MM



The handle can be assembled to a subrack or 19" front panel. Available with clear or black anodized surface. Handles will be bolted from the rear side.

CERTIFICATIONS



FEATURES

Static load-carrying capacity 30 kg/pair

Bolted from rear

SPECIFICATIONS

Table 1/2

Katalognum mer	Handle Type	Package Quantity	Typ	Product Type	Product Family	Fungerar med
10501-116	Rak	1	Straight version	Handle	EuropacPRO	Subracks
10501-004	Rak	1	Straight version	Handle	EuropacPRO	Subracks
10501-020	Angled Handle	1	Angled version	Handle	EuropacPRO	Subracks
10501-026	Rak	1	Straight version	Handle	EuropacPRO	Subracks
10501-005	Rak	1	Straight version	Handle	EuropacPRO	Subracks
10501-006	Rak	1	Straight version	Handle	EuropacPRO	Subracks
10501-007	Rak	1	Straight version	Handle	EuropacPRO	Subracks
10501-022	Angled Handle	1	Angled version	Handle	EuropacPRO	Subracks

Katalognummer	Handle Type	Package Quantity	Typ	ProductType	Product Family	Fungerar med
10501-029	Rak	1	Straight version	Handle	EuropacPRO	Subracks
10501-008	Rak	1	Straight version	Handle	EuropacPRO	Subracks
10501-016	Rak	1	Straight version	Handle	EuropacPRO	Subracks
10501-021	Angled Handle	1	Angled version	Handle	EuropacPRO	Subracks
10501-018	Rak	1	Straight version	Handle	EuropacPRO	Subracks
10501-025	Rak	1	Straight version	Handle	EuropacPRO	Subracks
10501-027	Rak	1	Straight version	Handle	EuropacPRO	Subracks
10501-028	Rak	1	Straight version	Handle	EuropacPRO	Subracks

Table 2/2					
Katalognummer	Rack Height	Färg	Material	Tillbehörstyp	Vridmoment
10501-116	1 U	Silver	Aluminium	Front panel	
10501-004	2 U	Silver	Aluminium	Front panel	
10501-020	3 U	Silver	Aluminium		2.4 N·m
10501-026	3 U	Svart	Aluminium	Front panel	2.4 N·m
10501-005	3 U	Silver	Aluminium		2.4 N·m
10501-006	4 U	Silver	Aluminium	Front panel	
10501-007	5 U	Silver	Aluminium	Front panel	
10501-022	6 U	Silver	Aluminium		2.4 N·m
10501-029	6 U	Svart	Aluminium	Front panel	2.4 N·m
10501-008	6 U	Silver	Aluminium		2.4 N·m
10501-016	2 U	Silver	Aluminium	Front panel	
10501-021	4 U	Silver	Aluminium		2.4 N·m
10501-018	4 U	Silver	Aluminium	Front panel	2.4 N·m
10501-025	2 U	Svart	Aluminium	Front panel	
10501-027	4 U	Svart	Aluminium	Front panel	
10501-028	5 U	Svart	Aluminium	Front panel	

ADDITIONAL PRODUCT DETAILS

Please order assembly part kit separately.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER