

FRONT PANEL, UNSHIELDED, WITH FASTENER PIN



Front panel with GND/earthing connection. The grounding can be done with a cable which fits to the fastener pin on the rear side of the panel.

CERTIFICATIONS



FEATURES

Enable grounding of the front area (protection class 1)

SPECIFICATIONS

Table 1/3

Katalognummer	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width	Package Quantity
20119-159	Nej	Anodized	Conductive	Nej	7 HP	1
20119-160	Nej	Anodized	Conductive	Nej	14 HP	1
20119-161	Nej	Anodized	Conductive	Nej	21 HP	1
20119-162	Nej	Anodized	Conductive	Nej	28 HP	1
20119-163	Nej	Anodized	Anodized	Nej	42 HP	1

Table 2/3

Katalognummer	Höjd	Product Type	Typ	Rack Height	Bredd	Uppfyller kraven enligt
---------------	------	--------------	-----	-------------	-------	-------------------------

20119-159	128.4 mm	Front Panel	Front Panel without Handle	3 U	35.2 mm	IEC 60297-3-101, IEEE 1101.1/10
20119-160	128.4 mm	Front Panel	Front Panel without Handle	3 U	70.8 mm	IEC 60297-3-101, IEEE 1101.1/10
20119-161	128.4 mm	Front Panel	Front Panel without Handle	3 U	106.3 mm	IEC 60297-3-101, IEEE 1101.1/10
20119-162	128.4 mm	Front Panel	Front Panel without Handle	3 U	141.9 mm	IEC 60297-3-101, IEEE 1101.1/10
20119-163	128.4 mm	Front Panel	Front Panel without Handle	3 U	213 mm	IEC 60297-3-101, IEEE 1101.1/10

Table 3/3

Katalognummer	Montering	Material
20119-159	Screw-on Front	Aluminium
20119-160	Screw-on Front	Aluminium
20119-161	Screw-on Front	Aluminium
20119-162	Screw-on Front	Aluminium
20119-163	Screw-on Front	Aluminium

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER