

CABLE TO WEB OF RAIL COMPLETE WELDER, POWER



功能

Complete web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis

Includes mold cleaner and flint ignitor

技术参数

材料: Graphite; Steel; Thermoplastic

绑线终端样式: W

Table 1/2						
物料号	轨道类型	Handle Clamp	导体公称外径	焊机式样	焊药	方向
PBWH301RH	UIC60	C105C, Sold Separately	8.89mm	T20	PB65, Sold Separately	Right Hand
PBWT202JLH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	12.19mm	T20	PB90, Sold Separately	Left Hand
PBWT202JRH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	12.19mm	T20	PB90, Sold Separately	Right Hand
PBWT20X5LH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	15.52mm	T20	PB150, Sold Separately	Left Hand
PBWT20X5RH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	15.52mm	T20	PB150, Sold Separately	Right Hand

物料号	轨道类型	Handle Clamp	导体公称外径	焊机式样	焊药	方向
PBWT202WLH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	19.05mm	T20	PB115, Sold Separately	Left Hand
PBWT202WRH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	19.05mm	T20	PB115, Sold Separately	Right Hand
PBWT203SLH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	26.42mm	T20	PB250, Sold Separately	Left Hand
PBWT203SRH	85 lb to 141 lb T-Rail Sections	C105C, Sold Separately	26.42mm	T20	PB250, Sold Separately	Right Hand

Table 2/2	
物料号	导体尺寸
PBWY301RH	50 mm ² Concentric
PBWT202JLH	2/0 Ropelay
PBWT202JRH	2/0 Ropelay
PBWT20X5LH	95 mm ² Ropelay
PBWT20X5RH	95 mm ² Ropelay
PBWT202WLH	250 kcmil Ropelay
PBWT202WRH	250 kcmil Ropelay
PBWT203SLH	500 kcmil Ropelay
PBWT203SRH	500 kcmil Ropelay

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

⚠ WARNING: This product can expose you to chemicals including diisononyl phthalate, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov.



Our powerful portfolio of brands:
[nVent.com](https://www.nVent.com) CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.