

SOCKET STRIP, IEC C13, WITH WIELAND® INPUT



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

CERTIFICATIONS



功能

Input via Wieland® GST 18 plug

Installation height 1 U

In accordance with IEC 60320

Horizontal or vertical mounting

Output via IEC 60320 C-13 sockets

Socket strips can be rotated through all four directions (in 90° increments) during fitting

技术参数

Table 1/2

物料号	产品类型	插座类型	Socket Quantity	Switched Outlets	颜色	交流电压
60110-340	Socket Strip	IEC C13	12	No	Grey	230V
60110-341	Socket Strip	IEC C13	12	No	Black	230V

物料号	产品类型	插座类型	Socket Quantity	Switched Outlets	颜色	交流电压
60110-342	Socket Strip	IEC C13	12	No	Red	230V
60110-349	Socket Strip	IEC C13	6	No	Grey	230V
60110-350	Socket Strip	IEC C13	6	No	Black	230V
60110-351	Socket Strip	IEC C13	6	No	Red	230V

Table 2/2						
物料号	功能	长度	深度	表面处理	材料	包装数量
60110-340		438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-341		438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-342		438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-349	Overcurrent Protection	438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-350	Overcurrent Protection	438.5mm	44mm	Anodized	Aluminum, Polyamide	1
60110-351	Overcurrent Protection	438.5mm	44mm	Anodized	Aluminum, Polyamide	1

ADDITIONAL PRODUCT DETAILS

Please order mounting bracket for vertical mounting separately.

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。



Our powerful portfolio of brands:
[nVent.com](https://www.nVent.com) CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.