

# TELECOM MAIN GROUNDING BUSBAR



## CERTIFICATIONS



## FUNKTIONER

- Meets TIA-607-C and TIA-607-D and conforms to BICSI® recommendations
- Complies with NEMA® standards
- Accepts two hole lugs with 5/16" or 7/16" bolt holes (hardware not included)
- Telecom grounding busbar splice kits are available to extend the length of the busbar

## SPEKIFIKATIONER

- Thickness (T):** 6.35mm
- Width (W):** 101.6mm
- Materiale:** Copper

| Table 1/2     |               |               |             |                             |                             |        |
|---------------|---------------|---------------|-------------|-----------------------------|-----------------------------|--------|
| Katalognummer | Length 1 (L1) | Length 2 (L2) | Tin Plating | Hole Size 1 Number of Pairs | Hole Size 2 Number of Pairs | C      |
| TMGBA12L15P   | 305mm         | 229mm         | No          | 15                          | 3                           | 15.9mm |
| TMGBA12L15PT  | 305mm         | 229mm         | Yes         | 15                          | 3                           | 15.9mm |

| Katalognummer | Length 1(L1) | Length 2(L2) | Tin Plating | Hole Size 1<br>Number of<br>Pairs | Hole Size 2<br>Number of<br>Pairs | C      |
|---------------|--------------|--------------|-------------|-----------------------------------|-----------------------------------|--------|
| TMGBA20L27P   | 508mm        | 229mm        | No          | 27                                | 3                                 | 15.9mm |
| TMGBA24L33PT  | 610mm        | 457mm        | Yes         | 33                                | 5                                 | 15.9mm |
| TMGBA29L41PT  | 737mm        | 457mm        | Yes         | 41                                | 5                                 | 15.9mm |

Table 2/2

| Katalognummer | B      | A      | D      | Hole Size 1<br>(HS1) | Hole Size 2<br>(HS2) |
|---------------|--------|--------|--------|----------------------|----------------------|
| TMGBA12L15P   | 28.6mm | 25.4mm | 15.9mm | 0.3125in             | 0.4375in             |
| TMGBA12L15PT  | 28.6mm | 25.4mm | 15.9mm | 0.3125in             | 0.4375in             |
| TMGBA20L27P   | 28.6mm | 25.4mm | 15.9mm | 0.3125in             | 0.4375in             |
| TMGBA24L33PT  | 28.6mm | 25.4mm | 15.9mm | 0.3125in             | 0.4375in             |
| TMGBA29L41PT  | 28.6mm | 25.4mm | 15.9mm | 0.3125in             | 0.4375in             |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**