

NVENT ERIFLEX FLEXBUS HCBC PLATE WITH PE CONNECTION



CERTIFICATIONS



VLASTNOSTI

Rigid tinned copper part provides strong electrical contact to maintain braid expansion during compression

HCBC Plate allows Flexbus Conductor insulation to overlap the connection palm

HCBC Plate with PE connection allows conductor to be added to interconnect neutral and ground/earth

Tinned copper allows for copper or aluminum conductor connections

Installs quickly and easily

RoHS compliant

SPECIFIKACE

Materiál: Copper

Povrchová úprava: Tinned

Table 1/2

Katalogové číslo	Article Number	E	Thickness (T)	Conductor Size	A	Hole Size 2 (HS2)
FLEXPLATE100 PE	508183	70mm	5mm	960 mm ² , 1280 mm ² , 1810 mm ²	115mm	18.5mm


Katalogové číslo	Article Number	E	Thickness(T)	Conductor Size	A	Hole Size 2 (HS2)
FLEXPLATE50PE	508182	70mm	5mm	220 mm ² , 360 mm ² , 545 mm ² , 640 mm ²	65mm	14.5mm

Table 2/2						
Katalogové číslo	Article Number	Hole Size 1 (HS1)	B	Unit Weight	C	D
FLEXPLATE100PE	508183	12.5mm	100mm	0.71kg	45mm	51mm
FLEXPLATE50PE	508182	10.5mm	100mm	0.49kg	45mm	41mm

ADDITIONAL PRODUCT DETAILS

It is mandatory to use the HCBC Clamp associated with the HCBC Plate for proper Flexbus Conductor connection.

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER