

## ABS ADJUSTABLE BUSBAR SUPPORT INSULATOR MODULE



### CERTIFICATIONS



### FEATURES

Modules provide flexibility to select distance between phases and supports

Extremely robust construction

Halogen free insulators

RoHS compliant

### SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Typical Application Current Rating	Busbars per Phase	Busbar Thickness	Busbar Width	Max Working Voltage, IEC (Ui)
ABS1-5MOD	560860	1,700 A Max	1	5 mm	50 – 125 mm	1,000 VAC, 1,500 VDC

Table 2/2


Catalog Number	Article Number	Working Temperature	Width (W)	Unit Weight
----------------	----------------	---------------------	-----------	-------------

ABS1-5MOD	560860	-40 to 130 °C	74 mm	0.640 kg
-----------	--------	---------------	-------	----------

### ADDITIONAL PRODUCT DETAILS

ABS Adjustable Busbar Support High Ampacity Kit available to support up to 200 mm (7.87") busbar width for applications up to 7400 A.

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**