



NVENT CADDY SPEED LINK SLK WITH LOOP



CERTIFICATIONS



FEATURES

- Complete system includes wire, locking device and pre-assembled loop end fitting
- Easy and flexible solution attaches to building structures
- Wire rope wraps around structure and through loop for quick installation
- Ideal for attaching to purlins, beams and other structural members
- Works well in tight or confined spaces
- Loop attaches directly to pipe, ductwork or other hanging assemblies

SPECIFICATIONS

- Static Load Safety Factor:** 5:1
- Finish:** Electrogalvanized
- Material:** Steel;Polypropylene;Zinc Alloy
- Complies With:** SMACNA HVAC-DCS

Table 1/2						
Catalog Number	Wire Rope Diameter	Wire Rope Length	Length (L)	Height (H)	Width (W)	Thickness (T)

SLK15L1LP	1.5 mm	1m	101.6 mm	55 mm	19 mm	12.5 mm
SLK15L1LPR2	1.5 mm	1m	101.6 mm	55 mm	19 mm	12.5 mm
SLK15L2LP	1.5 mm	2m	101.6 mm	55 mm	19 mm	12.5 mm
SLK15L2LPR2	1.5 mm	2m	101.6 mm	55 mm	19 mm	12.5 mm
SLK15L3LP	1.5 mm	3m	101.6 mm	55 mm	19 mm	12.5 mm
SLK15L3LPR2	1.5 mm	3m	101.6 mm	55 mm	19 mm	12.5 mm
SLK15L5LP	1.5 mm	5m	101.6 mm	55 mm	19 mm	12.5 mm
SLK15L5LPR2	1.5 mm	5m	101.6 mm	55 mm	19 mm	12.5 mm
SLK15L7LP	1.5 mm	7m	101.6 mm	55 mm	19 mm	12.5 mm
SLK2L10LP	2 mm	10m	101.6 mm	55 mm	19 mm	12.5 mm
SLK2L1LP	2 mm	1m	101.6 mm	55 mm	19 mm	12.5 mm
SLK2L2LP	2 mm	2m	101.6 mm	55 mm	19 mm	12.5 mm
SLK2L3LP	2 mm	3m	101.6 mm	55 mm	19 mm	12.5 mm
SLK2L5LP	2 mm	5m	101.6 mm	55 mm	19 mm	12.5 mm
SLK3L10LP	3 mm	10m	101.6 mm	62 mm	24 mm	16 mm
SLK3L2LP	3 mm	2m	101.6 mm	62 mm	24 mm	16 mm
SLK3L3LP	3 mm	3m	101.6 mm	62 mm	24 mm	16 mm
SLK3L5LP	3 mm	5m	101.6 mm	62 mm	24 mm	16 mm

Table 2/2				
Catalog Number	Angle (a)	Static Load (F)	Packing Quantity	Certifications
SLK15L1LP	90 ° Max	195N	1.0000	cUL, UL, SMACNA
SLK15L1LPR2	90 ° Max	195N	2.0000	cUL, UL, SMACNA
SLK15L2LP	90 ° Max	195N	1.0000	cUL, UL, SMACNA
SLK15L2LPR2	90 ° Max	195N	2.0000	cUL, UL, SMACNA
SLK15L3LP	90 ° Max	195N	1.0000	cUL, UL, SMACNA
SLK15L3LPR2	90 ° Max	195N	2.0000	cUL, UL, SMACNA
SLK15L5LP	90 ° Max	195N	1.0000	cUL, UL, SMACNA
SLK15L5LPR2	90 ° Max	195N	2.0000	cUL, UL, SMACNA
SLK15L7LP	90 ° Max	195N	1.0000	cUL, UL, SMACNA
SLK2L10LP	90 ° Max	440N	1.0000	cUL, UL, SMACNA
SLK2L1LP	90 ° Max	440N	1.0000	cUL, UL, SMACNA
SLK2L2LP	90 ° Max	440N	1.0000	cUL, UL, SMACNA
SLK2L3LP	90 ° Max	440N	1.0000	cUL, UL, SMACNA
SLK2L5LP	90 ° Max	440N	1.0000	cUL, UL, SMACNA
SLK3L10LP	90 ° Max	890N	1.0000	SMACNA

Catalog Number	Angle (a)	Static Load (F)	Packing Quantity	Certifications
SLK3L2LP	90 ° Max	890N	1.0000	SMACNA
SLK3L3LP	90 ° Max	890N	1.0000	SMACNA
SLK3L5LP	90 ° Max	890N	1.0000	SMACNA

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500