

## IMPROVED NVENT CADDY CAT HP J-HOOK



nVent CADDY Cat HP J-Hooks are the foundation of the nVent CADDY Cat HP System. The revamped nVent CADDY Cat HP J-Hook offers contractors three unique, UL-certified attachment methods out of the box—wall, ceiling, and threaded rod installations. This added functionality enables contractors to reduce SKU inventory while maintaining efficiency and continued progress on the jobsite with the most common structural attachment methods.

The modernized design of the nVent CADDY Cat HP J-Hook is engineered to provide optimal support and protection for today's rapidly evolving, high-performing low voltage cable. Contractors can feel confident utilizing the nVent CADDY Cat HP J-Hook due to its installation versatility, superior cable support and protection, and technical certifications.

### CERTIFICATIONS



### FEATURES

Versa-Mount Technology: Innovative attachment design provides multiple structural and installation methods for wall, ceiling, and threaded rod mounting applications

Ideal for unknown jobsite applications or attachment methods

Improved design allows for optimized inventory while reducing job site scheduling risks associated with multiple SKUs

Provides optimal support for high-performance data cable—including category cable, Power over Ethernet (PoE), and fiber optic

Industry-leading bend radius designed to protect high-performance data installations

Multiple color options aid in the identification and organization of the pathway application

Provides superior fill capacity and load rating

Compliant with UL® 2043 and suitable for use in air handling (plenum) spaces

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

Complies with EN 50174-2

## SPECIFICATIONS

Table 1/2

Catalog Number	Cable Capacity, Cat 6A	Cable Capacity, Cat 5e	Cable Capacity, Cat 6	Height 1 (H1)	Height 2 (H2)	Diameter (Ø)
CAT16HP	10	20	15	108.9mm	90.2mm	25mm
CAT21HP	25	50	40	122.2mm	103.6mm	33.3mm
CAT32HP	35	90	60	130.8mm	112.3mm	50mm
CAT32HPBA	35	90	60	130.8mm	112.3mm	50mm
CAT32HPBU	35	90	60	130.8mm	112.3mm	50mm
CAT32HPGR	35	90	60	130.8mm	112.3mm	50mm
CAT32HPOR	35	90	60	130.8mm	112.3mm	50mm
CAT32HPRD	35	90	60	130.8mm	112.3mm	50mm
CAT32HPWH	35	90	60	130.8mm	112.3mm	50mm
CAT32HPYL	35	90	60	130.8mm	112.3mm	50mm
CAT48HP	80	200	150	164.6mm	148.8mm	75mm
CAT64HP	140	330	220	188.5mm	180mm	100mm

Table 2/2

Catalog Number	Area	Static Load (F)	Color	Material	Finish
CAT16HP	690mm <sup>2</sup>	267N		Steel	Pregalvanized
CAT21HP	1174mm <sup>2</sup>	267N		Steel	Pregalvanized
CAT32HP	2561mm <sup>2</sup>	267N		Steel	Pregalvanized
CAT32HPBA	2561mm <sup>2</sup>	267N	Black	Steel	Pregalvanized, Painted
CAT32HPBU	2561mm <sup>2</sup>	267N	Blue	Steel	Pregalvanized, Painted
CAT32HPGR	2561mm <sup>2</sup>	267N	Green	Steel	Pregalvanized, Painted
CAT32HPOR	2561mm <sup>2</sup>	267N	Orange	Steel	Pregalvanized, Painted
CAT32HPRD	2561mm <sup>2</sup>	267N	Red	Steel	Pregalvanized, Painted
CAT32HPWH	2561mm <sup>2</sup>	267N	White	Steel	Pregalvanized, Painted
CAT32HPYL	2561mm <sup>2</sup>	267N	Yellow	Steel	Pregalvanized, Painted
CAT48HP	5974mm <sup>2</sup>	267N		Steel	Pregalvanized
CAT64HP	9987mm <sup>2</sup>	267N		Steel	Pregalvanized

## ADDITIONAL PRODUCT DETAILS


---

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

Cable capacity is calculated based on a 70% fill rate.

## DIAGRAMS

---



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**