

## TD COMPACT FOUR POLE DISTRIBUTION BLOCK, 80/100 A



### CERTIFICATIONS



### FEATURES

Minimum space for maximum power

Protection cover and insulating screens are transparent

Insulating screen between each row

Easy and safe connections

Easily clips onto DIN rail or mounts to panel with screws

Solid bars provide reliability

Wiring with or without terminal

RoHS compliant

Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22

Halogen free

### SPECIFICATIONS

**Material:** Thermoplastic; Brass

Table 1/4

| Catalog Number | Article Number | Max Current Rating, IEC | Peak Short Circuit Current (I <sub>pk</sub> ) | Line Side Stranded Wire Size - Ferrule | Line Side Compact Stranded Wire Size | Short Term Withstand Current (I <sub>cw</sub> ) 1s |
|----------------|----------------|-------------------------|---|--|--------------------------------------|--|
| TD-80-100A     | 563920         | 100A                    | 20kA  | 10 – 25mm <sup>2</sup>                 | 10 - 25 mm <sup>2</sup>              | 4.5kA  |
| TD-80-100AL    | 563930         | 100A                    | 20kA  | 10 – 25mm <sup>2</sup>                 | 10 - 25 mm <sup>2</sup>              | 4.5kA  |
| TD-80-100ALL   | 563940         | 100A                    | 20kA  | 10 – 25mm <sup>2</sup>                 | 10 - 25 mm <sup>2</sup>              | 4.5kA  |

Table 2/4

| Catalog Number | Article Number | Line Side Number of Connections | Load Side Number of Connections | Load Side Compact Stranded Wire Size                         | Load Side Stranded Wire Size - Ferrule                     | Max Working Voltage, IEC (Ui) |
|----------------|----------------|---------------------------------|---------------------------------|--|--|-------------------------------|
| TD-80-100A     | 563920         | 1                               | 6                               | (3) 1,5 - 4 mm <sup>2</sup> ,<br>(3) 2,5 - 6 mm <sup>2</sup> | (3) 0,75 – 4 mm <sup>2</sup> , (3) 1,5 – 6 mm <sup>2</sup> | 500V                          |
| TD-80-100AL    | 563930         | 2                               | 9                               | (4) 1,5 - 4 mm <sup>2</sup> ,<br>(5) 2,5 - 6 mm <sup>2</sup> | (4) 0,75 – 4 mm <sup>2</sup> , (5) 1,5 – 6 mm <sup>2</sup> | 500V                          |
| TD-80-100ALL   | 563940         | 2                               | 13                              | (6) 1,5 - 4 mm <sup>2</sup> ,<br>(7) 2,5 - 6 mm <sup>2</sup> | (6) 0,75 – 4 mm <sup>2</sup> , (7) 1,5 – 6 mm <sup>2</sup> | 500V                          |

Table 3/4

| Catalog Number | Article Number | Height (H) | Width (W) | Depth (D) | Unit Weight | Flammability Rating |
|----------------|----------------|------------|-----------|-----------|-------------|---------------------|
| TD-80-100A     | 563920         | 90mm       | 64mm      | 50mm      | 0.21kg      | UL® 94V-0           |
| TD-80-100AL    | 563930         | 90mm       | 100mm     | 50mm      | 0.31kg      | UL® 94V-0           |
| TD-80-100ALL   | 563940         | 90mm       | 130mm     | 50mm      | 0.4kg       | UL® 94V-0           |

Table 4/4


| Catalog Number | Article Number | Complies With  |
|----------------|----------------|----------------|
| TD-80-100A     | 563920         | IEC® 60947-7-1 |
| TD-80-100AL    | 563930         | IEC® 60947-7-1 |
| TD-80-100ALL   | 563940         | IEC® 60947-7-1 |

## ADDITIONAL PRODUCT DETAILS

Line side and load side number of connections are per pole.

| Design Guideline for Distribution Blocks, Power Blocks and Power Terminals              |     |     |     |      |      |      |      |      |      |      |
|---|-----|-----|-----|------|------|------|------|------|------|------|
| Derating according to Ambient* Temperature (°C) to maintain working temperature of 85°C |     |     |     |      |      |      |      |      |      |      |
| Ambient Temperature (°C)  | 30° | 35° | 40° | 45°  | 50°  | 55°  | 60°  | 65°  | 70°  | 75°  |
| Derating Coefficient (d)  | 1   | 1   | 1   | 0.94 | 0.88 | 0.82 | 0.75 | 0.67 | 0.58 | 0.47 |
| *environment around the terminal blocks inside the enclosure                            |     |     |     |      |      |      |      |      |      |      |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

[nVent.com](http://nVent.com) CADDY ERICO HOFFMAN RAYCHEM SCHROFF

TRACER