



115M STANDARD DUTY LOOP HANGER



The 115M Standard Duty Loop Hanger is ideal for suspending stationary, non-insulated pipe lines, including CPVC pipes, in fire sprinkler systems. A knurled insert nut helps simplify vertical adjustments and flared edges on the base (1/2" to 4" sizes) help protect pipes from coming into contact with any sharp edges of the hanger.

CERTIFICATIONS



FEATURES

Flared edges help prevent any sharp surfaces from coming into contact with the pipe (1/2" to 4" sizes)

Retained insert nut helps ensure the loop hanger and insert nut stay together

Recommended for the suspension of stationary non-insulated pipe lines

Manufactured to use the minimum rod size permitted by NFPA® for fire sprinkler piping

Conforms with Federal Specification WW-H-171 (Type 10), Manufacturers Standardization Society (MSS) SP-58 (Type 10)

SPECIFICATIONS

Finish: Pregalvanized

Material: Steel

Table 1/2


Catalog Number	Article Number	Pipe Size	Pipe Size Range	NB/DN	Outer Diameter (OD)	Rod Size (RS)
115M0050EG	597860	1/2"	0.5 in	15	21.3 mm	M10
115M0075EG	597870	3/4"	0.75 in	20	26.9 mm	M10

Catalog Number	Article Number	Pipe Size	Pipe Size Range	NB/DN	Outer Diameter (OD)	Rod Size(RS)
115M0200EG	597910	2"	2 in min	50	60.3 mm	M10
115M0100EG	597880	1"	1 in	25	33.7 mm	M10
115M0125EG	597890	1 1/4"	1.25 in min	32	42.4 mm	M10
115M0150EG	597900	1 1/2"	1.5 in	40	48.3 mm	M10
115M0400EG	597940	4"	4 in	100	114 mm	M10
115M0300EG	597930	3"	3 in	80	89 mm	M10
115M0250EG	597920	2 1/2"	2.5 in	65	76 mm	M10
115M0500EG	597950	5"	5 in	125	140 mm	M12
115M0800EG	597970	8"	8 in	200	219 mm	M12
115M0600EG	597960	6"	6 in	150	165 mm	M12

Table 2/2						
Catalog Number	Article Number	A	B	C	Ultimate Static Load (F)	Certifications
115M0050EG	597860	71 mm	28.6 mm	25.4 mm	5000N	cUL, ITB, UL
115M0075EG	597870	75.9 mm	30.2 mm	23.9 mm	5000N	cUL, FM Approved, Pipe Hanger Components, ITB, UL
115M0200EG	597910	108.6 mm	47.6 mm	23.9 mm	5000N	cUL, FM Approved, Pipe Hanger Components, ITB, UL
115M0100EG	597880	82.5 mm	34.9 mm	24.1 mm	5000N	cUL, FM Approved, Pipe Hanger Components, ITB, UL
115M0125EG	597890	90.6 mm	38.1 mm	24.1 mm	5000N	cUL, FM Approved, Pipe Hanger Components, ITB, UL
115M0150EG	597900	96.7 mm	41.3 mm	24.1 mm	5000N	cUL, FM Approved, Pipe Hanger Components, ITB, UL

Catalog Number	Article Number	A	B	C	Ultimate Static Load (F)	Certifications
115M0400EG	597940	192.5 mm	100.9 mm	48.9 mm	14000N	cUL, FM Approved, Pipe Hanger Components, ITB, UL
115M0300EG	597930	166.3 mm	88.2 mm	49.7 mm	14000N	cUL, FM Approved, Pipe Hanger Components, ITB, UL
115M0250EG	597920	150.8 mm	87.3 mm	50.8 mm	14000N	cUL, FM Approved, Pipe Hanger Components, ITB, UL
115M0500EG	597950	232.7 mm	120 mm	57.1 mm	20000N	cUL, FM Approved, Pipe Hanger Components, ITB, UL
115M0800EG	597970	327.1 mm	175.1 mm	73.4 mm	20000N	cUL, FM Approved, Pipe Hanger Components, ITB, UL
115M0600EG	597960	286.6 mm	160.4 mm	84.1 mm	20000N	cUL, FM Approved, Pipe Hanger Components, ITB, UL

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER