


## FOUR POLE DISTRIBUTION BLOCK WITH THREADED BARS, 250 A

### CATALOG NUMBER

**TR-250A**



### CERTIFICATIONS



### FEATURES

Easily fixes onto asymmetric DIN rail or mounts with screws

Bolts included for output connections

Transparent protection cover

Easy accessibility for wiring

Ready to use out of the box, saving installation time and labor

RoHS compliant

### PRODUCT ATTRIBUTES

Article Number: 563170

Material: Copper; Glass Fibre Reinforced Polyamide; Plexiglass

Max Working Voltage, IEC (Ui): 630

Peak Short Circuit Current (I<sub>pk</sub>): 34kA

Short Term Withstand Current (I<sub>cw</sub>) 1s: 17kA

Line Side Number of Connections: 2

Load Side Number of Connections: 4

Hole Size (HS): 8mm

Thread Size (TS): M6

Depth (D): 68mm

Height (H): 150mm

Width (W): 230mm

Unit Weight: 1.3kg

Flammability Rating: UL® 94V-0

Complies With: IEC® 60439.1; IEC® 61439.1; IEC® 60695-2-11 (Glow Wire Test 960 °C)


## ADDITIONAL PRODUCT DETAILS

---

Line side and load side number of connections are per pole.

## DIAGRAMS

---



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**