

FRONT PANEL, UNSHIELDED, BOTTOM HINGED

Unshielded front panel bottom hinged.



CERTIFICATIONS



FEATURES

Front panel can be unhinged at 135° (not RatiopacPRO) opening angle

Enables mounting on horizontal rails

SPECIFICATIONS

Accessory Type: Front panel

Table 1/3

Catalog Number	Type	Mounting	EMC Shielding	Material	Front Finish	Rear Finish
20838-280	Front Panel without Handle	Hinged, Bottom	No	Aluminum	Anodized	Conductive
20838-271	Front Panel without Handle	Hinged, Bottom	No	Aluminum	Anodized	Conductive
20838-272	Front Panel without Handle	Hinged, Bottom	No	Aluminum	Anodized	Conductive
20838-273	Front Panel without Handle	Hinged, Bottom	No	Aluminum	Anodized	Conductive

Catalog Number	Type	Mounting	EMC Shielding	Material	Front Finish	Rear Finish
20838-277	Front Panel without Handle	Hinged, Bottom	No	Aluminum	Anodized	Conductive
20838-278	Front Panel without Handle	Hinged, Bottom	No	Aluminum	Anodized	Conductive
20838-279	Front Panel without Handle	Hinged, Bottom	No	Aluminum	Anodized	Conductive
20838-276	Front Panel without Handle	Hinged, Bottom	No	Aluminum	Anodized	Conductive
20838-275	Front Panel without Handle	Hinged, Bottom	No	Aluminum	Anodized	Conductive
20838-274	Front Panel without Handle	Hinged, Bottom	No	Aluminum	Anodized	Conductive

Table 2/3						
Catalog Number	Treated Edges	Rack Height	Height (H)	Rack Width	Width (W)	Complies With
20838-280	No	3U	128.4mm	28HP	141.9mm	IEC 60297-3-101, IEEE 1101.1/10
20838-271	No	3U	128.4mm	42HP	213mm	IEC 60297-3-101, IEEE 1101.1/10
20838-272	No	3U	128.4mm	63HP	319.7mm	IEC 60297-3-101, IEEE 1101.1/10
20838-273	No	3U	128.4mm	84HP	426.4mm	IEC 60297-3-101, IEEE 1101.1/10
20838-277	No	4U	172.9mm	42HP	213mm	IEC 60297-3-101, IEEE 1101.1/10
20838-278	No	4U	172.9mm	63HP	319.7mm	IEC 60297-3-101, IEEE 1101.1/10
20838-279	No	4U	172.9mm	84HP	426.4mm	IEC 60297-3-101, IEEE 1101.1/10
20838-276	No	6U	261.8mm	84HP	426.4mm	IEC 60297-3-101, IEEE 1101.1/10
20838-275	No	6U	261.8mm	63HP	319.7mm	IEC 60297-3-101, IEEE 1101.1/10

Catalog Number	Treated Edges	Rack Height	Height (H)	Rack Width	Width (W)	Complies With
20838-274	No	6U	261.8mm	42HP	213mm	IEC 60297-3-101, IEEE 1101.1/10


Table 3/3

Catalog Number	Package Quantity	Finish
20838-280	1	Anodized
20838-271	1	Anodized
20838-272	1	Anodized
20838-273	1	Anodized
20838-277	1	Anodized
20838-278	1	Anodized
20838-279	1	Anodized
20838-276	1	Anodized
20838-275	1	Anodized
20838-274	1	Anodized

ADDITIONAL PRODUCT DETAILS

Front panel can be removed in opened position (> 135°).

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER