

112 LOOP HANGER WITH FLARED EDGES



CERTIFICATIONS



FEATURES

For steel and CPVC pipe

Flared edges help to protect plastic pipe

An integral fold-over washer (pipe sizes 2 1/2" to 8")

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/2

Catalog Number	Article Number	Pipe Size	NB/DN	Outer Diameter (OD)	Rod Size (RS)	A
1120050EG		1/2"	15	21 mm	3/8"	70.7 mm
1120075EG		3/4"	20	27 mm	3/8"	76.4 mm
1120100EG		1"	25	34 mm	3/8"	83.7 mm
1120125EG		1 1/4"	32	43 mm	3/8"	92.1 mm

Catalog Number	Article Number	Pipe Size	NB/DN	Outer Diameter (OD)	Rod Size(RS)	A
1120150EG		1 1/2"	40	48 mm	3/8"	98.2 mm
1120200EG		2"	50	60 mm	3/8"	110.2 mm
1120250EG		2 1/2"	65	76 mm	3/8"	138.2 mm
1120300EG		3"	80	89 mm	3/8"	154.1 mm
1120400EG		4"	100	114 mm	3/8"	193.8 mm
112M0050EG	297860	1/2"	15	21.3 mm	M10	70.7 mm
1120500EG		5"	125	140 mm	1/2"	236.2 mm
1120600EG		6"	150	165 mm	1/2"	262.7 mm
1120800EG		8"	200	219 mm	1/2"	337.6 mm
112B0500EG		5"	125	141 mm	1/2"	236.2 mm
112B0600EG		6"	150	165 mm	1/2"	262.7 mm
112B0800EG		8"	200	219 mm	1/2"	337.6 mm
112M0100EG	297880	1"	25	26.9 mm	M10	83.8 mm
112M0125EG	297890	1 1/4"	32	42.4 mm	M10	92.1 mm
112M0150EG	297900	1 1/2"	40	48.3 mm	M10	98.2 mm
112M0200EG	297910	2"	50	60.3 mm	M10	110.2 mm
112M0075EG	297870	3/4"	20	26.9 mm	M10	76.4 mm
112M0250EG	297920	2 1/2"	65	76.1 mm	M10	138.2 mm
112M0300EG	297930	3"	80	88.9 mm	M10	154.1 mm
112M0400EG	297940	4"	100	114.3 mm	M10	193.8 mm
112M0600EG	297960	6"	150	165 mm	M12	262.7 mm
112M0500EG	297950	5"	125	141 mm	M12	236.2 mm
112M0800EG	297970	8"	200	219.1 mm	M12	337.6 mm


Table 2/2

Catalog Number	Article Number	B	C	Static Load (F)	Certifications
1120050EG		29.2 mm	26.2 mm	1334N	cUL, UL
1120075EG		32.2 mm	26.5 mm	1334N	cUL, FM Approved, Pipe Hanger Components, UL
1120100EG		36.2 mm	27.1 mm	1334N	cUL, FM Approved, Pipe Hanger Components, UL

CatalogNumber	Article Number	B	C	Static Load (F)	Certifications
1120125EG		40.2 mm	26.7 mm	1334N	cUL, FM Approved, Pipe Hanger Components, UL
1120150EG		43.2 mm	26.7 mm	1334N	cUL, FM Approved, Pipe Hanger Components, UL
1120200EG		49.2 mm	26.7 mm	1334N	cUL, FM Approved, Pipe Hanger Components, UL
1120250EG		70.2 mm	41.3 mm	2340N	cUL, FM Approved, Pipe Hanger Components, UL
1120300EG		78.2 mm	41.4 mm	2340N	cUL, FM Approved, Pipe Hanger Components, UL
1120400EG		105.2 mm	55.7 mm	3780N	cUL, FM Approved, Pipe Hanger Components, UL
112M0050EG	297860	29.2 mm	26.2 mm	1330N	cUL, UL
1120500EG		125.9 mm	65.4 mm	3780N	cUL, FM Approved, Pipe Hanger Components, UL
1120600EG		138.9 mm	64.9 mm	3500N	cUL, FM Approved, Pipe Hanger Components, UL
1120800EG		187.9 mm	88.5 mm	6000N	cUL, FM Approved, Pipe Hanger Components, UL
112B0500EG		125.9 mm	65.4 mm	4440N	
112B0600EG		138.9 mm	64.9 mm	4440N	
112B0800EG		187.9 mm	88.5 mm	4440N	
112M0100EG	297880	36.2 mm	27.1 mm	1330N	cUL, FM Approved, Pipe Hanger Components, UL
112M0125EG	297890	40.2 mm	26.7 mm	1330N	cUL, FM Approved, Pipe Hanger Components, UL
112M0150EG	297900	43.2 mm	26.7 mm	1330N	cUL, FM Approved, Pipe Hanger Components, UL
112M0200EG	297910	49.2 mm	26.7 mm	1330N	cUL, FM Approved, Pipe Hanger Components, UL

CatalogNumber	Article Number	B	C	Static Load (F)	Certifications
112M0075EG	297870	32.2 mm	26.5 mm	1330N	cUL, FM Approved, Pipe Hanger Components, UL
112M0250EG	297920	70.2 mm	41.3 mm	2340N	cUL, FM Approved, Pipe Hanger Components, UL
112M0300EG	297930	78.2 mm	41.4 mm	2340N	cUL, FM Approved, Pipe Hanger Components, UL
112M0400EG	297940	105.2 mm	55.7 mm	2890N	cUL, FM Approved, Pipe Hanger Components, UL
112M0600EG	297960	138.9 mm	64.9 mm	4450N	cUL, FM Approved, Pipe Hanger Components, UL
112M0500EG	297950	125.9 mm	65.4 mm	2890N	cUL, FM Approved, Pipe Hanger Components, UL
112M0800EG	297970	187.9 mm	88.5 mm	6000N	cUL, FM Approved, Pipe Hanger Components, UL

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER