



# NVENT CADDY PYRAMID H-FRAME POST BASE



## FEATURES

- Foam or rubber bottom offers low abrasion interface for better roof membrane protection
- Compatible with roof surfaces including single ply, bituminous, metal and spray foam
- Provides superior load distribution, even with varying rooftop surfaces
- Rubber rooftop interface ideal for solar panel array installations
- Mounting hardware pre-installed in bases
- Hot-dip galvanized and UV stabilized for long lasting performance
- Accepts standard strut channels

## SPECIFICATIONS


- Static Load Safety Factor:** 3:1
- Finish:** Hot-Dip Galvanized
- Material:** Steel;Polypropylene;Polyethylene
- Temperature:** -34 to 54.4 °C

Table 1/2						
Catalog Number	Article Number	Rooftop Interface	Strut Type	Height (H)	Length (L)	Width (W)
PHB	360422	Foam	A (41 x 41 mm)	117 mm	314 mm	314 mm
PHBR	360423	Rubber	A (41 x 41 mm)	118 mm	314 mm	314 mm

Table 2/2				
Catalog Number	Article Number	Surface Area	Unit Weight	Static Load (F)

PHB	360422	0.09m <sup>2</sup>	1.8 kg	3335N
PHBR	360423	0.1m <sup>2</sup>	2 kg	3335N

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**  
+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

**Europe**  
Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**  
Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**  
Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500