

## REPLACEMENT MODULE FOR DSD, 10 KA



### CERTIFICATIONS




### SPECIFICATIONS

Catalog Number	DSD110M275
Article Number	702566
Nominal System Voltage (Un)	220 - 240 V
Max Continuous Operating Voltage (Uc)	275 VAC 350 VDC
Nominal Discharge Current (In), Per Mode	5kA 8/20 $\mu$ s
Max Discharge Current (Imax), Per Mode	10kA 8/20 $\mu$ s
Voltage Protection Level (Up)	930 V @ 3 kA 1300 V @ 5 kA
Frequency	0 - 60 Hz
Technology	MOV with thermal disconnect
Enclosure Material	UL® 94V-0 Thermoplastic
Status Indication	Mechanical flag
Temperature	-40 to 80 °C
Module Width	1 M
Depth (D)	49mm

Catalog Number	DSD110M275
Height (H)	45 mm
Width (W)	18 mm
Unit Weight	0.07 kg

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**  
+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

**Europe**  
Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**  
Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**  
Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500