

VARISTAR CP SERVER CABINET WITH CASTORS



Welded steel frame for high dynamic load requirements.
Prepared for 19" integration of IT assets.

FEATURES

Preconfigured, ready to use cabinet

High dynamic load 1000 kg with integrated castors, static load-carrying capacity up to 1600 kg

Ingress protection class IP 20

Installation of different IT equipment possible

Integrated air panels for front to back cooling

Can be easily integrated into aisle containment system

SPECIFICATIONS

Table 1/3

Catalog Number	Type	Cladding Material	Frame Material	Cladding Color	Cladding Color Code	Static Load
10630-021	Mobile	Steel	Steel	Black Grey	RAL 7021	1600kgf
10630-022	Mobile	Steel	Steel	Black Grey	RAL 7021	1600kgf

Table 2/3

Catalog Number	Dynamic Load	Product Type	Height	Rack Height	Package Quantity	Finish
10630-021	1000kgf	Rack	2000mm	42U	1	Powder Coated

Catalog Number	Dynamic Load	ProductType	Height	Rack Height	Package Quantity	Finish
10630-022	1000kgf	Rack	2000mm	42U	1	Powder Coated

Table 3/3			
Catalog Number	Material	Width	Depth
10630-021	Steel	600mm	1200mm
10630-022	Steel	800mm	1200mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER