



NVENT CADDY EZ RISER



The nVent CADDY EZ Riser is a multi-purpose clamp designed to secure and support vertical pipe runs. This unified solution can be installed in several approved orientations and serves as a standard, standoff, or close-quarters riser—effectively functioning as three clamps in one. Ready-to-use out of the box, the nVent CADDY EZ Riser features pre-drilled threaded rod holes for standoff installations and score marks for simple ear removal in spaces where full-sized riser clamps do not fit.

Contractors can enjoy simplified material handling with a multi-functional clamp that allows for various orientations and retains listing even when ears are removed.

CERTIFICATIONS



FEATURES

- Only one tool needed to tighten due to serrated wash-heads
- Installs up to 60% faster than standard riser clamps
- Integrated second set of bolt holes allow the assembly to adapt from a riser clamp into a stand-off support easily
- No need to stock and use separate part families for standard and close-quarter clamps to offer a full range of listed parts
- Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 (Type 8)

SPECIFICATIONS

- Finish:** Electrogalvanized
- Material:** Steel

Table 1/2						
Catalog Number	Article Number	Pipe Size	Outer Diameter (OD)	Hole Size (HS)	A	B
EZR0250	179231	2 1/2"	73 mm	9.9 mm	279.4 mm	190.5 mm

Catalog Number	Article Number	Pipe Size	Outer Diameter (OD)	Hole Size (HS)	A	B
EZR0300	179232	3"	88.9 mm	9.9 mm	298.5 mm	206.4 mm
EZR0350	179233	3 1/2"	101.6 mm	13.2 mm	320.7 mm	238.1 mm
EZR0400	179234	4"	114.3 mm	13.2 mm	330.2 mm	254 mm
EZR0600	179236	6"	168.3 mm	13.2 mm	406.4 mm	323.9 mm

Table 2/2


Catalog Number	Article Number	C	Static Load (F)
EZR0250	179231	25.4 mm	1735N
EZR0300	179232	25.4 mm	2400N
EZR0350	179233	31.8 mm	2980N
EZR0400	179234	31.8 mm	3600N
EZR0600	179236	38.1 mm	6900N

ADDITIONAL PRODUCT DETAILS

Clamp is fitted for steel pipe and should be installed below a coupling or shear lug, with bolts torqued to recommended value.

Use of a socket or driver is recommended for installation.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER