


NVENT ERICO PERMAGROUND COMPRESSION CONNECTOR, C-CRIMPS



The nVent ERICO PermaGround Compression Connector, C-Crimps are high-strength, conductive copper connectors designed to create permanent, low-resistance grounding connections. These C-Crimps utilize a compression tool to join two grounding conductors securely, and their range-taking design accommodates various conductor sizes. Clear markings and all-weather durability make them ideal for diverse applications, including direct burial.

FEATURES

- Dies are interchangeable with tools from nVent ILSCO TaskMaster and other manufacturers per product instructions
- Permanent, corrosion-free grounding with high-conductivity copper ensures lasting, reliable connections
- Adaptable to various conductor sizes, simplifying inventory and maximizing application flexibility
- Engineered for reliable environmental performance, including direct burial in earth or concrete
- Clear imperial markings and die index simplify installation
- Suitable for circuits rated 35 kV or less with proper installation
- Manufactured from high-conductivity copper alloy

SPECIFICATIONS


Table 1/2						
Catalog Number	Material	Conductor Type	Main/Run Conductor Range	Tap Conductor Range	Connection Type	Number of Crimps
ULT-1-MM	Copper	Solid, Stranded	4 - 4 mm ²	4 - 4 mm ²	Conductor to Conductor	1
ULT-2-MM	Copper	Solid, Stranded	10 - 6 mm ²	6 - 6 mm ²	Conductor to Conductor	1
ULT-3-MM	Copper	Stranded	25 - 16 mm ²	10 - 10 mm ²	Conductor to Conductor	1
ULT-4-MM	Copper	Solid, Stranded	25 - 16 mm ²	16 - 16 mm ²	Conductor to Conductor	1
ULT-5-MM	Copper	Stranded	25 - 16 mm ²	25 - 25 mm ²	Conductor to Conductor	1

Catalog Number	Material	Conductor Type	Main/Run Conductor Range	Tap Conductor Range	Connection Type	Number of Crimps
ULT-7-MM	Copper	Stranded, Stranded	35 - 35 mm ²	35 - 35 mm ²	Conductor to Conductor	2
ULT-6-MM	Copper	Stranded	35 - 35 mm ²	25 - 10 mm ²	Conductor to Conductor	2
ULT-8-MM	Copper	Stranded	70 - 50 mm ²	35 - 10 mm ²	Conductor to Conductor	3
ULT-9-MM	Copper	Solid, Stranded	70 - 50 mm ²	70 - 50 mm ²	Conductor to Conductor	1
ULT-11-MM	Copper	Stranded	120 - 95 mm ²	70 - 50 mm ²	Conductor to Conductor	1
ULT-10-MM	Copper	Solid, Stranded	95 - 95 mm ²	25 - 16 mm ²	Conductor to Conductor	1
ULT-12-MM	Copper	Stranded	95 - 95 mm ²	95 - 95 mm ²	Conductor to Conductor	1

Table 2/2

Catalog Number	Length (L)	Width (W)	Height (H)	Unit Weight	Direct Burial
ULT-1-MM	9.3 mm	7.1 mm	8.7 mm	0.002 kg	Yes
ULT-2-MM	12.3 mm	9 mm	12.7 mm	0.006 kg	Yes
ULT-3-MM	18.7 mm	11.9 mm	15.6 mm	0.015 kg	Yes
ULT-4-MM	19.4 mm	11.7 mm	17.8 mm	0.019 kg	Yes
ULT-5-MM	21.1 mm	11.9 mm	17.8 mm	0.019 kg	Yes
ULT-7-MM	26.6 mm	15.6 mm	21 mm	0.037 kg	Yes
ULT-6-MM	25.1 mm	15.6 mm	21.1 mm	0.039 kg	Yes
ULT-8-MM	34.3 mm	20.6 mm	23.5 mm	0.07 kg	Yes
ULT-9-MM	34.3 mm	20.6 mm	23.5 mm	0.07 kg	Yes
ULT-11-MM	41.4 mm	25.4 mm	27.3 mm	0.12 kg	Yes
ULT-10-MM	41.4 mm	25.4 mm	27.3 mm	0.14 kg	Yes
ULT-12-MM	40.9 mm	25.4 mm	30.5 mm	0.14 kg	Yes

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER