


TD COMPACT FOUR POLE DISTRIBUTION BLOCK, 100/125 A



CERTIFICATIONS



FEATURES

- Minimum space for maximum power
- Protection cover and insulating screens are transparent
- Insulating screen between each row
- Easy and safe connections
- Easily clips onto DIN rail or mounts to panel with screws
- Solid bars provide reliability
- Input separated from outputs
- Strong mechanical assembly
- Neutral bar available
- RoHS compliant
- Conforms to EN 45545 obtaining an HL3 classification for chapter R23 and HL2 classification for chapter R22
- Halogen free

SPECIFICATIONS

| | | | |
|-----------------------|---------------------|---------------------|----------------------|
| Material: | Thermoplastic;Brass | | |
| Catalog Number | TD-100-125A | TD-100-125AL | TD-100-125ALL |


| | | | |
|--|--|--|--|
| Article Number | 563820 | 563830 | 563840 |
| Max Current Rating, IEC | 125A | 125A | 125A |
| Short Term Withstand Current (Icw) 1s | 4.5kA | 4.5kA | 4.5kA |
| Peak Short Circuit Current (Ipk) | 30kA | 30kA | 21kA |
| Max Working Voltage, IEC (Ui) | 690V | 690V | 690V |
| Line Side Number of Connections | 1 | 1 | 1 |
| Line Side Compact Stranded Wire Size | 10 - 35 mm ² | 10 - 35 mm ² | 10 - 35 mm ² |
| Line Side Stranded Wire Size - Ferrule | 10 - 35 mm ² | 10 - 35 mm ² | 10 - 35 mm ² |
| Load Side Number of Connections | 6 | 10 | 14 |
| Load Side Compact Stranded Wire Size | (5) 2,5 - 6 mm ² (1) 10 - 25 mm ² | (7) 2,5 - 6 mm ² (3) 10 - 25 mm ² | (11) 2,5 - 6 mm ² (1) 10 - 25 mm ² (2) 10 - 35 mm ² |
| Load Side Stranded Wire Size - Ferrule | (5) 1,5 - 6 mm ² (1) 6 - 16 mm ² | (7) 1,5 - 6 mm ² (3) 6 - 16 mm ² | (11) 1,5 - 6 mm ² (1) 6 - 16 mm ² (2) 10 - 25 mm ² |
| Depth (D) | 50mm | 50mm | 50mm |
| Height (H) | 90 mm | 90 mm | 90 mm |
| Width (W) | 109 mm | 147 mm | 182 mm |
| Unit Weight | 0.33 kg | 0.44 kg | 0.55 kg |
| Flammability Rating | UL® 94V-0 | UL® 94V-0 | UL® 94V-0 |
| Complies With | IEC® 60947-7-1 | IEC® 60947-7-1 | IEC® 60947-7-1 |

ADDITIONAL PRODUCT DETAILS

Line side and load side number of connections are per pole.

| Design Guideline for Distribution Blocks, Power Blocks and Power Terminals | | | | | | | | | | |
|---|-----|-----|-----|------|------|------|------|------|------|------|
| Derating according to Ambient* Temperature (°C) to maintain working temperature of 85°C | | | | | | | | | | |
| Ambient Temperature (°C) | 30° | 35° | 40° | 45° | 50° | 55° | 60° | 65° | 70° | 75° |
| Derating Coefficient (d) | 1 | 1 | 1 | 0.94 | 0.88 | 0.82 | 0.75 | 0.67 | 0.58 | 0.47 |
| *environment around the terminal blocks inside the enclosure | | | | | | | | | | |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER