



# UNIVERSAL STRUCTURAL ATTACHMENT



## CERTIFICATIONS



## FEATURES

- Universal design allows one product to attach directly to concrete, wood, bar joist or I-beam adapters
- Snap-off bolt head helps enable easy installation and inspection of seismic sway braces
- Use for both lateral and longitudinal sway brace applications
- Works with 1" through 2" brace pipes and 1/4" angle iron braces to reduce inventory
- Center bolt does not require tightening
- Meets NFPA®-13 requirements for seismic sway bracing
- Meets CEN/TS 17551:2021 requirements for Seismic Sway Bracing

## SPECIFICATIONS

| Table 1/2      |                |          |        |                |   |   |
|----------------|----------------|----------|--------|----------------|---|---|
| Catalog Number | Article Number | Material | Finish | Hole Size (HS) | A | B |

|              |        |           |                   |       |          |          |
|--------------|--------|-----------|-------------------|-------|----------|----------|
| CSBUNIV050EG | 404407 | Cast Iron | Electrogalvanized | 14 mm | 133.4 mm | 101.6 mm |
| CSBUNIV075EG | 404409 | Cast Iron | Electrogalvanized | 21 mm | 133.4 mm | 101.6 mm |


Table 2/2

| Catalog Number | Article Number | C       | Certifications   |
|----------------|----------------|---------|--|
| CSBUNIV050EG   | 404407         | 41.4 mm | AON Fire Protection, Rigid Seismic, Korea Fire Institute, Rigid Seismic, KOR, cUL, UL, OSHPD, FM Approved, Seismic |
| CSBUNIV075EG   | 404409         | 41.4 mm | AON Fire Protection, Rigid Seismic, cUL, UL, OSHPD, FM Approved, Seismic   |

| UL Loads     |                        |        |
|--------------|------------------------|--------|
| Part number  | Brace Member           | Rating |
| CSBUNIV050EG | 25 mm - 50 mm EN10255H | 6094 N |
| CSBUNIV075EG | 25 mm - 50 mm EN10255H | 8896 N |

| FM Loads   |                   |  |          |          |          |
|------------|-------------------|--|----------|----------|----------|
| Brace Type | Service Pipe Size | Horizontal Capacity per Installation Angle from Vertical |          |          |          |
|            |                   | 30°- 44°   | 45°- 59° | 60°- 74° | 75°- 90° |
| Pipe       | N/A               | 7,205 N  | 10,230 N | 12,545 N | 13,965 N |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**