



112 LOOP HANGER WITH FLARED EDGES



CERTIFICATIONS



FEATURES

For steel and CPVC pipe

Flared edges help to protect plastic pipe

An integral fold-over washer (pipe sizes 2 1/2" to 8")

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel

Table 1/2

Catalog Number	Article Number	Pipe Size	Pipe Size Range	NB/DN	Outer Diameter (OD)	Rod Size (RS)
1120050EG		1/2"	0.5 in	15	21 mm	3/8"
1120075EG		3/4"	0.75 in	20	27 mm	3/8"
1120100EG		1"	1 in	25	34 mm	3/8"
1120125EG		1 1/4"	1.25 in min	32	43 mm	3/8"


Catalog Number	Article Number	Pipe Size	Pipe Size Range	NB/DN	Outer Diameter (OD)	Rod Size(RS)
1120150EG		1 1/2"	1.5 in	40	48 mm	3/8"
1120200EG		2"	2 in min	50	60 mm	3/8"
1120250EG		2 1/2"	2.5 in	65	76 mm	3/8"
1120300EG		3"	3 in	80	89 mm	3/8"
1120400EG		4"	4 in	100	114 mm	3/8"
112M0050EG	297860	1/2"	0.5 in	15	21.3 mm	M10
1120500EG		5"	5 in	125	140 mm	1/2"
1120600EG		6"	6 in	150	165 mm	1/2"
1120800EG		8"	8 in	200	219 mm	1/2"
112B0500EG		5"	5 in	125	141 mm	1/2"
112B0600EG		6"	6 in	150	165 mm	1/2"
112B0800EG		8"	8 in	200	219 mm	1/2"
112M0100EG	297880	1"	1 in	25	26.9 mm	M10
112M0125EG	297890	1 1/4"	1.25 in min	32	42.4 mm	M10
112M0150EG	297900	1 1/2"	1.5 in	40	48.3 mm	M10
112M0200EG	297910	2"	2 in min	50	60.3 mm	M10
112M0075EG	297870	3/4"	0.75 in	20	26.9 mm	M10
112M0250EG	297920	2 1/2"	2.5 in	65	76.1 mm	M10
112M0300EG	297930	3"	3 in	80	88.9 mm	M10
112M0400EG	297940	4"	4 in	100	114.3 mm	M10
112M0600EG	297960	6"	6 in	150	165 mm	M12
112M0500EG	297950	5"	5 in	125	141 mm	M12
112M0800EG	297970	8"	8 in	200	219.1 mm	M12

Table 2/2						
Catalog Number	Article Number	A	B	C	Static Load (F)	Certifications
1120050EG		70.7 mm	29.2 mm	26.2 mm	1334N	cUL, UL
1120075EG		76.4 mm	32.2 mm	26.5 mm	1334N	cUL, FM Approved, Pipe Hanger Components, UL
1120100EG		83.7 mm	36.2 mm	27.1 mm	1334N	cUL, FM Approved, Pipe Hanger Components, UL

Catalog Number	Article Number	A	B	C	Static Load (F)	Certifications
1120125EG		92.1 mm	40.2 mm	26.7 mm	1334N	cUL, FM Approved, Pipe Hanger Components, UL
1120150EG		98.2 mm	43.2 mm	26.7 mm	1334N	cUL, FM Approved, Pipe Hanger Components, UL
1120200EG		110.2 mm	49.2 mm	26.7 mm	1334N	cUL, FM Approved, Pipe Hanger Components, UL
1120250EG		138.2 mm	70.2 mm	41.3 mm	2340N	cUL, FM Approved, Pipe Hanger Components, UL
1120300EG		154.1 mm	78.2 mm	41.4 mm	2340N	cUL, FM Approved, Pipe Hanger Components, UL
1120400EG		193.8 mm	105.2 mm	55.7 mm	3780N	cUL, FM Approved, Pipe Hanger Components, UL
112M0050EG	297860	70.7 mm	29.2 mm	26.2 mm	1330N	cUL, UL
1120500EG		236.2 mm	125.9 mm	65.4 mm	3780N	cUL, FM Approved, Pipe Hanger Components, UL
1120600EG		262.7 mm	138.9 mm	64.9 mm	3500N	cUL, FM Approved, Pipe Hanger Components, UL
1120800EG		337.6 mm	187.9 mm	88.5 mm	6000N	cUL, FM Approved, Pipe Hanger Components, UL
112B0500EG		236.2 mm	125.9 mm	65.4 mm	4440N	
112B0600EG		262.7 mm	138.9 mm	64.9 mm	4440N	
112B0800EG		337.6 mm	187.9 mm	88.5 mm	4440N	
112M0100EG	297880	83.8 mm	36.2 mm	27.1 mm	1330N	cUL, FM Approved, Pipe Hanger Components, UL

Catalog Number	Article Number	A	B	C	Static Load (F)	Certifications
112M0125EG	297890	92.1 mm	40.2 mm	26.7 mm	1330N	cUL, FM Approved, Pipe Hanger Components, UL
112M0150EG	297900	98.2 mm	43.2 mm	26.7 mm	1330N	cUL, FM Approved, Pipe Hanger Components, UL
112M0200EG	297910	110.2 mm	49.2 mm	26.7 mm	1330N	cUL, FM Approved, Pipe Hanger Components, UL
112M0075EG	297870	76.4 mm	32.2 mm	26.5 mm	1330N	cUL, FM Approved, Pipe Hanger Components, UL
112M0250EG	297920	138.2 mm	70.2 mm	41.3 mm	2340N	cUL, FM Approved, Pipe Hanger Components, UL
112M0300EG	297930	154.1 mm	78.2 mm	41.4 mm	2340N	cUL, FM Approved, Pipe Hanger Components, UL
112M0400EG	297940	193.8 mm	105.2 mm	55.7 mm	2890N	cUL, FM Approved, Pipe Hanger Components, UL
112M0600EG	297960	262.7 mm	138.9 mm	64.9 mm	4450N	cUL, FM Approved, Pipe Hanger Components, UL
112M0500EG	297950	236.2 mm	125.9 mm	65.4 mm	2890N	cUL, FM Approved, Pipe Hanger Components, UL
112M0800EG	297970	337.6 mm	187.9 mm	88.5 mm	6000N	cUL, FM Approved, Pipe Hanger Components, UL

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER