



IMPROVED NVENT CADDY CAT HP J-HOOK



nVent CADDY Cat HP J-Hooks are the foundation of the nVent CADDY Cat HP System. The revamped nVent CADDY Cat HP J-Hook offers contractors three unique, UL-certified attachment methods out of the box—wall, ceiling, and threaded rod installations. This added functionality enables contractors to reduce SKU inventory while maintaining efficiency and continued progress on the jobsite with the most common structural attachment methods.

The modernized design of the nVent CADDY Cat HP J-Hook is engineered to provide optimal support and protection for today's rapidly evolving, high-performing low voltage cable. Contractors can feel confident utilizing the nVent CADDY Cat HP J-Hook due to its installation versatility, superior cable support and protection, and technical certifications.

CERTIFICATIONS



FEATURES

Versa-Mount Technology: Innovative attachment design provides multiple structural and installation methods for wall, ceiling, and threaded rod mounting applications

Ideal for unknown jobsite applications or attachment methods

Improved design allows for optimized inventory while reducing job site scheduling risks associated with multiple SKUs

Provides optimal support for high-performance data cable—including category cable, Power over Ethernet (PoE), and fiber optic

Industry-leading bend radius designed to protect high-performance data installations

Multiple color options aid in the identification and organization of the pathway application

Provides superior fill capacity and load rating

Compliant with UL® 2043 and suitable for use in air handling (plenum) spaces

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

Complies with EN 50174-2

SPECIFICATIONS

Table 1/2

Catalog Number	Material	Finish	Color	Diameter (Ø)	Area	Cable Capacity, Cat 5e
CAT16HP	Steel	Pregalvanized		1"	1.07in ²	20
CAT21HP	Steel	Pregalvanized		1 5/16"	2.29in ²	50
CAT32HP	Steel	Pregalvanized		2"	4.22in ²	90
CAT32HPBA	Steel	Pregalvanized, Painted	Black	2"	4.22in ²	90
CAT32HPBU	Steel	Pregalvanized, Painted	Blue	2"	4.22in ²	90
CAT32HPGR	Steel	Pregalvanized, Painted	Green	2"	4.22in ²	90
CAT32HPOR	Steel	Pregalvanized, Painted	Orange	2"	4.22in ²	90
CAT32HPRD	Steel	Pregalvanized, Painted	Red	2"	4.22in ²	90
CAT32HPWH	Steel	Pregalvanized, Painted	White	2"	4.22in ²	90
CAT32HPYL	Steel	Pregalvanized, Painted	Yellow	2"	4.22in ²	90
CAT48HP	Steel	Pregalvanized		3"	9.26in ²	200
CAT64HP	Steel	Pregalvanized		4"	15.48in ²	330

Table 2/2

Catalog Number	Cable Capacity, Cat 6	Cable Capacity, Cat 6A	Height 1 (H1)	Height 2 (H2)	Static Load (F)
CAT16HP	15	10	4.29	3.55	60lb
CAT21HP	40	25	4.81	4.08	60lb
CAT32HP	60	35	5.15	4.42	60lb
CAT32HPBA	60	35	5.15	4.42	60lb
CAT32HPBU	60	35	5.15	4.42	60lb
CAT32HPGR	60	35	5.15	4.42	60lb
CAT32HPOR	60	35	5.15	4.42	60lb
CAT32HPRD	60	35	5.15	4.42	60lb
CAT32HPWH	60	35	5.15	4.42	60lb
CAT32HPYL	60	35	5.15	4.42	60lb
CAT48HP	150	80	6.48	5.86	60lb

CatalogNumber	CableCapacity, Cat 6	CableCapacity, Cat6A	Height 1 (H1)	Height 2 (H2)	Static Load (F)
CAT64HP	220	140	7.42	7.09	60lb


ADDITIONAL PRODUCT DETAILS

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

Cable capacity is calculated based on a 70% fill rate.

				Capacity(70% Fill)				
Cable	Number of Twisted Pairs	AWG	Cable Diameter	CAT16HP	CAT21HP	CAT32HP	CAT48HP	CAT64HP
UTP	4	24	0.197 in	20	30	70	160	280
FTP	4	24	0.236 in	15	20	50	110	190
SFTP	4	24	0.236 in	15	20	50	110	190
SFTP	4	23	0.276 in	10	15	40	85	140
F/STP	4	23	0.335 in	7	10	25	60	100
SFTP	4	23	0.335 in	7	10	25	60	100
SFTP	3x4	24	0.551 in	2	4	9	20	35
UTP	25	24	0.512 in	3	5	11	25	40

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER