



NVENT CADDY PYRAMID H-FRAME POST BASE



FEATURES

- Foam or rubber bottom offers low abrasion interface for better roof membrane protection
- Compatible with roof surfaces including single ply, bituminous, metal and spray foam
- Provides superior load distribution, even with varying rooftop surfaces
- Rubber rooftop interface ideal for solar panel array installations
- Mounting hardware pre-installed in bases
- Hot-dip galvanized and UV stabilized for long lasting performance
- Accepts standard strut channels

SPECIFICATIONS

- Static Load Safety Factor:** 3:1
- Finish:** Hot-Dip Galvanized
- Material:** Steel;Polypropylene;Polyethylene
- Temperature:** -30 to 130 °F


Table 1/2

Catalog Number	Rooftop Interface	Strut Type	Height (H)	Length (L)	Width (W)	Surface Area
PHB	Foam	A (1 5/8" x 1 5/8")	4.6"	12 3/8"	12 3/8"	144in ²
PHBR	Rubber	A (1 5/8" x 1 5/8")	4.66"	12 3/8"	12 3/8"	144in ²

Table 2/2

Catalog Number	Unit Weight	Static Load (F)
PHB	3.9 lb	750lb
PHBR	4.5 lb	750lb

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER