


TR FOUR POLE DISTRIBUTION BLOCK, 125 A



CERTIFICATIONS



FEATURES

- Easily clips onto DIN rail or mounts to panel with screws
- Equipped with a current input plug
- Bolts included for output connections
- Transparent protection cover
- Easy accessibility for wiring
- Ready to use out of the box, saving installation time and labor
- RoHS compliant

SPECIFICATIONS

Table 1/3						
Catalog Number	Article Number	Peak Short Circuit Current (Ipk)	Material	Short Term Withstand Current (Icw) 1s	Line Side Number of Connections	Load Side Number of Connections

TR-125A	563150	40kA	Copper, Glass Fibre Reinforced Polyamide, Plexiglass	8.4kA	1	5
---------	--------	------	---	-------	---	---

Table 2/3

Catalog Number	Article Number	Max Working Voltage, IEC (Ui)	Thread Size 1 (TS1)	Thread Size 2 (TS2)	Height (H)	Width (W)
TR-125A	563150	1000	M5	M6	4.96in	5.91in

Table 3/3


Catalog Number	Article Number	Depth (D)	Unit Weight	Flammability Rating	Complies With
TR-125A	563150	4.61in	1.51lb	UL® 94V-0	IEC® 60439.1, IEC® 61439.1, IEC® 60695-2-11 (Glow Wire Test 960 °C)

ADDITIONAL PRODUCT DETAILS

Thread Size 2 represents input plug.

Line side and load side number of connections are per pole.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER