


FRONT PANEL, U-PROFILE, REFROFIT SHIELDING



U-profile front panel for textile EMC gasket.

CERTIFICATIONS



CARACTERÍSTICAS

U-profile, front panel, Aluminum, 2.5 mm, front anodized, rear conductive

For EMC textile gasket

ESPECIFICACIONES

Table 1/3

Número de catálogo	EMC Gasket Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
20848-047	Textile	No	Anodizado	Conductive	No (Retrofittable)	42 HP
20848-068	Textile	No	Anodizado	Conductive	No (Retrofittable)	63 HP
20848-097	Textile	No	Anodizado	Conductive	No (Retrofittable)	84 HP
20848-139	Textile	No	Anodizado	Conductive	No (Retrofittable)	42 HP

Número de catálogo	EMC Gasket Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
20848-160	Textile	No	Anodizado	Conductive	No (Retrofittable)	63 HP
20848-189	Textile	No	Anodizado	Conductive	No (Retrofittable)	84 HP
20848-260	Textile	No	Anodizado	Conductive	No (Retrofittable)	42 HP
20848-261	Textile	No	Anodizado	Conductive	No (Retrofittable)	63 HP
20848-262	Textile	No	Anodizado	Conductive	No (Retrofittable)	84 HP
20848-268	Textile	No	Anodizado	Conductive	No (Retrofittable)	28 HP
20848-269	Textile	No	Anodizado	Conductive	No (Retrofittable)	42 HP
20848-270	Textile	No	Anodizado	Conductive	No (Retrofittable)	42 HP
20848-271	Textile	No	Anodizado	Conductive	No (Retrofittable)	84 HP
20848-280	Textile	No	Anodizado	Conductive	No (Retrofittable)	84 HP
20848-648	Textile	No	Anodizado	Conductive	No (Retrofittable)	42 HP
20848-649	Textile	No	Anodizado	Conductive	No (Retrofittable)	63 HP
20848-650	Textile	No	Anodizado	Conductive	No (Retrofittable)	84 HP
30849-001	Textile	No	Anodizado	Conductive	No (Retrofittable)	2 HP
30849-002	Textile	No	Anodizado	Conductive	No (Retrofittable)	2 HP
20848-013	Textile	No	Anodizado	Conductive	No (Retrofittable)	14 HP
20848-015	Textile	No	Anodizado	Conductive	No (Retrofittable)	16 HP
20848-020	Textile	No	Anodizado	Conductive	No (Retrofittable)	21 HP
20848-027	Textile	No	Anodizado	Conductive	No (Retrofittable)	28 HP
30848-354	Textile	No	Anodizado	Conductive	No (Retrofittable)	4 HP

Número de catálogo	EMC Gasket Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
30848-356	Textile	No	Anodizado	Conductive	No (Retrofittable)	8 HP
30848-358	Textile	No	Anodizado	Conductive	No (Retrofittable)	12 HP
30848-378	Textile	No	Anodizado	Conductive	No (Retrofittable)	5 HP
30848-380	Textile	No	Anodizado	Conductive	No (Retrofittable)	6 HP
30848-382	Textile	No	Anodizado	Conductive	No (Retrofittable)	7 HP
30848-386	Textile	No	Anodizado	Conductive	No (Retrofittable)	10 HP
30849-004	Textile	No	Anodizado	Conductive	No (Retrofittable)	3 HP
30848-355	Textile	No	Anodizado	Conductive	No (Retrofittable)	4 HP
30848-379	Textile	No	Anodizado	Conductive	No (Retrofittable)	5 HP
20848-106	Textile	No	Anodizado	Conductive	No (Retrofittable)	14 HP
20848-108	Textile	No	Anodizado	Conductive	No (Retrofittable)	16 HP
20848-113	Textile	No	Anodizado	Conductive	No (Retrofittable)	21 HP
20848-120	Textile	No	Anodizado	Conductive	No (Retrofittable)	28 HP
30848-357	Textile	No	Anodizado	Conductive	No (Retrofittable)	8 HP
30848-359	Textile	No	Anodizado	Conductive	No (Retrofittable)	12 HP
30848-381	Textile	No	Anodizado	Conductive	No (Retrofittable)	6 HP
30848-383	Textile	No	Anodizado	Conductive	No (Retrofittable)	7 HP
30848-387	Textile	No	Anodizado	Conductive	No (Retrofittable)	10 HP

Table 2/3						
Número de catálogo	Package Quantity	Altura	Product Type	Tipo	Rack Height	Ancho

20848-047	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	213 mm
20848-068	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	319.7 mm
20848-097	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	426.4 mm
20848-139	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	213 mm
20848-160	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	319.7 mm
20848-189	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	426.4 mm
20848-260	1	84 mm	Front Panel	Front Panel without Handle	2 U	213 mm
20848-261	1	84 mm	Front Panel	Front Panel without Handle	2 U	319.7 mm
20848-262	1	84 mm	Front Panel	Front Panel without Handle	2 U	426.4 mm
20848-268	1	172.9 mm	Front Panel	Front Panel without Handle	4 U	141.9 mm
20848-269	1	172.9 mm	Front Panel	Front Panel without Handle	4 U	213 mm
20848-270	1	172.9 mm	Front Panel	Front Panel without Handle	4 U	213 mm
20848-271	1	172.9 mm	Front Panel	Front Panel without Handle	4 U	426.4 mm
20848-280	1	395.1 mm	Front Panel	Front Panel without Handle	9 U	426.4 mm
20848-648	1	217.4 mm	Front Panel	Front Panel without Handle	5 U	213 mm
20848-649	1	217.4 mm	Front Panel	Front Panel without Handle	5 U	319.7 mm
20848-650	1	217.4 mm	Front Panel	Front Panel without Handle	5 U	426.4 mm
30849-001	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	9.8 mm
30849-002	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	9.8 mm
20848-013	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	70.8 mm
20848-015	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	80.9 mm

20848-020	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	106.3 mm
20848-027	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	141.9 mm
30848-354	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	20 mm
30848-356	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	40.3 mm
30848-358	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	60.6 mm
30848-378	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	25 mm
30848-380	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	30.1 mm
30848-382	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	35.2 mm
30848-386	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	50.5 mm
30849-004	5	128.4 mm	Front Panel	Front Panel without Handle	3 U	14.9 mm
30848-355	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	20 mm
30848-379	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	25 mm
20848-106	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	70.8 mm
20848-108	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	80.9 mm
20848-113	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	106.3 mm
20848-120	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	141.9 mm
30848-357	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	40.3 mm
30848-359	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	60.6 mm
30848-381	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	30.1 mm
30848-383	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	35.2 mm
30848-387	5	261.8 mm	Front Panel	Front Panel without Handle	6 U	50.5 mm

Table 3/3

Número de catálogo	Cumple con	Montaje	Material	Certificaciones
20848-047	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-068	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-097	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-139	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-160	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-189	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-260	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	
20848-261	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	
20848-262	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-268	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-269	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-270	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-271	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-280	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-648	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	
20848-649	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	
20848-650	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	
30849-001	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
30849-002	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-013	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS

Número de catálogo	Cumple con	Montaje	Material	Certificaciones
20848-015	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-020	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-027	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
30848-354	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
30848-356	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
30848-358	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
30848-378	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
30848-380	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
30848-382	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
30848-386	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
30849-004	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
30848-355	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
30848-379	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-106	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-108	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-113	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
20848-120	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
30848-357	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
30848-359	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
30848-381	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS

Número de catálogo	Cumple con	Montaje	Material	Certificaciones
30848-383	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS
30848-387	IEC 60297-3-101, IEEE 1101.1/10	Screw-on Front	Aluminio	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

14 ... 84 HP: multi-part U-profile (front panel with crimped profiles).

Differences in finish between 2 ... 12 HP and 14 ... 84 HP.

2 ... 12 HP: one-part U-profile

Please order textile EMC gasket separately.

Standard pack quantity: 2 to 28HP: 5 pieces, 42 to 84 HP: 1 piece, supplied in standard pack quantities (SPQ) only.

ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Las hojas de instrucciones están disponibles en www.nvent.com y con su representante de atención al cliente de nVent. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.