

## GUARDIAN MANAGEMENT GATEWAY



The nVent SCHROFF Guardian Management Gateway is an environmental monitoring platform designed to sense, track, store and alarm health and security parameters in an IT data center infrastructure.

The heart of the platform is a compact control unit of 1 U in height/depth and 250 mm in width, it can be installed as 19" unit or into any available space in a data center rack.

The Management Gateway offers three sensor management ports with each port being able to monitor up to 16 sensor devices with a total cable length of 40 meters per port, allowing a single Management Gateway unit to monitor multiple racks or complete rack aisles.

Besides monitoring physical parameters like temperature, humidity, smoke, door status or water intrusion, the Management Gateway can also monitor nVent SCHROFF RackChiller and In- Row Coolers – with an easy plug and play installation.

Set-up of the Management Gateway with security features, sensor configuration, user management, alarm and log management can easily be done through a built-in Web Interface.

Main access to the Management Gateway is through the 1 GBE Network interface, supporting industry standard protocols like SNMP, SMTP, HTTPS, BACnet, Modbus/TCP and HPI.

### CERTIFICATIONS



### FEATURES

Data Center environmental monitoring platform

Compact design, fits anywhere in a data center rack

Web browser GUI for setup, monitoring and maintenance

Three management ports to connect external sensors and Modbus devices

Up to 16 sensors or devices per management port with a total cable length of up to 40 m

Auto orientation LCD touch display

## SPECIFICATIONS

| Table 1/3          |                  |                                 |                 |        |       |             |
|--------------------|------------------|---------------------------------|-----------------|--------|-------|-------------|
| Número de catálogo | Tipo de producto | Tipo                            | Altura del rack | Altura | Ancho | Profundidad |
| 11079-000          | Management Unit  | Base Unit<br>Management Gateway | 1U              | 45mm   | 250mm | 45mm        |
| 11079-001          | Management Unit  | Base Unit<br>Management Gateway | 1U              | 45mm   | 350mm | 45mm        |

| Table 2/3          |                       |                       |                      |                             |               |          |
|--------------------|-----------------------|-----------------------|----------------------|-----------------------------|---------------|----------|
| Número de catálogo | Voltaje de entrada AC | Voltaje de entrada DC | Temperatura ambiente | Humedad relativa            | Acabado       | Material |
| 11079-000          |                       | 12V min               | 5 – 60°C             | 5% to 90%,<br>Noncondensing | Powder Coated | Aluminio |
| 11079-001          | 100 – 240V            |                       | 5 – 60°C             | 5% to 90%,<br>Noncondensing | Powder Coated | Aluminio |

| Table 3/3          |                |
|--------------------|----------------|
| Número de catálogo | Certifications |
| 11079-000          | RoHS, WEEE     |
| 11079-001          |                |

## ADVERTENCIA

Los productos nVent deben instalarse y usarse solo como se indica en las hojas de instrucciones y materiales de capacitación del producto nVent. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. La instalación incorrecta, el mal uso, la aplicación incorrecta u otras fallas en el seguimiento completo de las instrucciones y advertencias de nVent pueden causar el mal funcionamiento del producto, daños a la propiedad, lesiones corporales graves y la muerte y/o anular la garantía.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**