


## ENLOGIC INPUT METERED, OUTLET SWITCHED PDU EN2 SERIES



The Advantage Series Input Metered, Outlet Switched PDU family offers energy metering with advanced power and environmental monitoring options and remote outlet on/off switching. Comprehensive monitoring at both the input phase and circuit breaker levels offers advanced alerts of potential overloads. Billing-grade metering provides accurate power consumption data for energy use optimization. The hot-swappable network management controller features Gigabit and redundant ethernet communication with advanced support for external environmental sensors and rack security access solutions.

### CARATTERISTICHE

IEC 62368 listed. RoHS, and REACH compliant. See drawing for additional information

UL 2900-1 certified for safety software cybersecurity for network-connectable products

Dual network connectivity ports: 1x Gigabit Ethernet (10/100/1000 Mbps) and 1x (10/100 Mbps) connection/IP address

Ethernet cascading up to 64 PDUs. Each PDU can provide DC power sufficient to power network management electronics

Dual Ethernet ports for redundant network communications

Remote connectivity through HTTP(s), IPv4 and IPv6, SSH, Virtual Serial, SNMP (v1, v2c, v3), JSON-RPC, LDAP(S)

Data efficient REACT framework with native mobile device support

Tool-less hot swappable Network Management Card (NMC) with Cortex A-5 for microprocessing and memory that can be installed both upright and upside down for top or bottom power inputs

The border color of the NMC display is user programmable for power source identification by PDU

The NMC supports up to 10 digital sensors for environmental and/or electronic lock monitoring

Display languages include English, Spanish, German, French, Italian, Korean, Japanese, and Chinese (simplified)

### SPECIFICHE

Table 1/6

| Codice a catalogo | Product Type | Famiglia di prodotti | Switched Outlets | Tipo            | Larghezza | Quantità per confezione |
|-------------------|--------------|----------------------|------------------|-----------------|-----------|-------------------------|
| EN2951            | Socket Strip | Enlogic              | Yes              | Intelligent PDU | 56mm      | 1                       |
| EN2990            | Socket Strip | Enlogic              | Yes              | Intelligent PDU | 85mm      | 1                       |

Table 2/6

| Codice a catalogo | Tipo di presa   | Socket Quantity | Colore | Altezza | Materiale | Finitura      |
|-------------------|---|-----------------|--------|---------|-----------|---------------|
| EN2951            | (21) C13/C15,<br>(21)<br>C13/C15/C19/C<br>21                    | 42              | Black  | 1826mm  | Steel     | Powder Coated |
| EN2990            | (24) Locking<br>C13/C15, (24)<br>Locking<br>C13/C15/C19/C<br>21 | 48              | Black  | 2030mm  | Steel     | Powder Coated |

Table 3/6

| Codice a catalogo | Profondità | Tensione nominale | Lunghezza del cavo | Rack Units | Numero di fasi | Circuit Breaker Quantity |
|-------------------|------------|-------------------|--------------------|------------|----------------|--------------------------|
| EN2951            | 75mm       | 208V              | 1800m              | 0U         | 3              | 6                        |
| EN2990            | 85mm       | 415V              | 1800m              | 0U         |                | 24                       |

Table 4/6

| Codice a catalogo | Current Rating | On/Off Switch Included | Number of Output Voltages | Circuit Breaker       | Metering Type | Nominal Power Output |
|-------------------|----------------|------------------------|---------------------------|-----------------------|---------------|----------------------|
| EN2951            | 14.4kV·A       | Yes                    | 42                        | 20 A, 2-pole, Hy-MagA | Input         | 208VAC               |
| EN2990            | 69kV·A         | Yes                    |                           | 20 A, 1-pole, Hy-MagA | Input         | 230VAC               |

Table 5/6

| Codice a catalogo | Removable Input Cable | Interrupt Rating | Peso | Plug Type                   | Input Cable Length | Tensione di ingresso   |
|-------------------|-----------------------|------------------|------|-----------------------------|--------------------|------------------------|
| EN2951            | No                    | 5kAIC            | 13kg | CS8365                      | 1.8m               | 208 VAC, 3 PH DeltaVAC |
| EN2990            | No                    |                  |      | IEC 60309<br>5125P6W (IP67) | 1.8m               |                        |

Table 6/6

| Codice a catalogo | Output Voltage |
|-------------------|----------------|
| EN2951            | 208VAC         |
| EN2990            | 208 – 230VAC   |

## ADDITIONAL PRODUCT DETAILS

---

Warranty : nVent Enlogic branded equipment provided shall be free from manufacturing defects for a period of five (5) years from the invoice date to the original purchaser.

## AVVERTIMENTO

---

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**