

NVENT ERIFLEX FLEXBUS HCBC PLATE WITH PE CONNECTION



CERTIFICATIONS



CARATTERISTICHE

Rigid tinned copper part provides strong electrical contact to maintain braid expansion during compression

HCBC Plate allows Flexbus Conductor insulation to overlap the connection palm

HCBC Plate with PE connection allows conductor to be added to interconnect neutral and ground/earth

Tinned copper allows for copper or aluminum conductor connections

Installs quickly and easily

RoHS compliant

SPECIFICHE

Materiale: Copper

Finitura: Tinned

Table 1/2

Codice a catalogo	Numero articolo	E	Spessore (T)	Dimensioni conduttore	A	Diametro del foro 2 (HS2)
FLEXPLATE100 PE	508183	70mm	5mm	960 mm ² , 1280 mm ² , 1810 mm ²	115mm	18.5mm


Codice a catalogo	Numero articolo	E	Spessore (T)	Dimensioni conduttore	A	Diametro del foro 2 (HS2)
FLEXPLATE50PE	508182	70mm	5mm	220 mm ² , 360 mm ² , 545 mm ² , 640 mm ²	65mm	14.5mm

Table 2/2						
Codice a catalogo	Numero articolo	Diametro del foro 1 (HS1)	B	Peso unitario	C	D
FLEXPLATE100PE	508183	12.5mm	100mm	0.71kg	45mm	51mm
FLEXPLATE50PE	508182	10.5mm	100mm	0.49kg	45mm	41mm

ADDITIONAL PRODUCT DETAILS

It is mandatory to use the HCBC Clamp associated with the HCBC Plate for proper Flexbus Conductor connection.

DIAGRAMS



AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER