

## RACKCHILLER IN-ROW 45



RackChiller In-Row Coolers (IRC) are designed to deliver localized/supplemental energy efficient cooling in data centers. The RackChiller In-Row 45 air-to liquid cooler is a modular and scalable precision cooling solution that can replace or supplement traditional data center cooling infrastructure. The units can be scaled optimally to suit individual packaging density and redundancy requirements.

The cooling system is integrated into a Varistar CP mobile frame for ideal side by side connection to Varistar CP or third party racks. The cooler comes with perforated front and rear doors. This allows seamless integration into rows of racks with hot or cold aisle containment. The integrated fans move the warm exhaust air from the hot aisle through an air to water heat exchanger where the heat is transferred to a water circuit. The air is then provided into the cold aisle towards the equipment.

### CARATTERISTICHE

In-Row air/liquid cooler, ideal for hot aisle containment

Hot-swappable components simplify repair and maximize availability

Designed for efficient operation at increased facility water temperatures

Combination with direct to chip liquid cooling

Modular standard - easy to adapt to individual requirements.

Minimum changes between In-Row and LHX+ (In-Rack) design - simplifies planning, layout and specification

Fans, power supplies, controller and control valve all are hot-swappable

Automatic fan speed and valve opening control

7" high resolution touch screen interface

Hydraulic and electric connection through top or bottom

Monitoring via Ethernet interface (Web browser, Modbus TCP, SNMP v2c) and Modbus RTU

### SPECIFICHE

Table 1/2

Codice a catalogo	Product Type	Famiglia di prodotti	Altezza	Profondità	Supply Voltage	Coolant Feed
10630-102	Air/Liquid Heat Exchanger	RackChiller	2000mm	1000mm	200 – 240V	Top

Codice a catalogo	ProductType	Famiglia di prodotti	Altezza	Profondità	Supply Voltage	CoolantFeed
10630-103	Air/Liquid Heat Exchanger	RackChiller	2000mm	1200mm	200 – 240V	Top, Bottom

Table 2/2						
Codice a catalogo	Rack Height	Larghezza	Grado di protezione	Materiale	Finitura	Quantità per confezione
10630-102	42U	300mm	IP20	Steel	Powder Coated	1
10630-103	42U	300mm	IP20	Steel	Powder Coated	1

## ADDITIONAL PRODUCT DETAILS

For trouble-free operation of the air/liquid heat exchanger the quality requirements of the coolant must be maintained; The selection of appropriate anti-corrosion and frost protection agents depends on the environment in which the unit is used and on the external chiller

At coolant temperatures below 14 °C, there is an increased risk of condensation. We recommend using a condensate management package

## AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**