

PLUG-IN UNIT KIT WITH TRAPEZOID HANDLE, UNSHIELDED, GREY



Plug-in unit, with static handle and the flat front panel. The grey handle is assembled on the front panel.

CERTIFICATIONS



CARATTERISTICHE

Flat front panel

Handle without extraction function

SPECIFICHE

Table 1/3


Codice a catalogo	Tipo	Tipo di maniglia	Montaggio	EMC Shielding	Materiale	Front Finish
20818-017	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	No	Aluminum	Anodized
20818-018	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	No	Aluminum	Anodized
20818-019	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	No	Aluminum	Anodized
20818-020	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	No	Aluminum	Anodized
20818-021	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	No	Aluminum	Anodized

Codice a catalogo	Tipo	Tipo di maniglia	Montaggio	EMC Shielding	Materiale	Front Finish
20818-022	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	No	Aluminum	Anodized
20818-023	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	No	Aluminum	Anodized
20818-024	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	No	Aluminum	Anodized
20818-025	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	No	Aluminum	Anodized
20818-026	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	No	Aluminum	Anodized
20818-027	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	No	Aluminum	Anodized
20818-028	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	No	Aluminum	Anodized
20818-029	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	No	Aluminum	Anodized
20818-120	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	No	Aluminum	Anodized
20818-162	Front Panel with Handle (PIU)	Trapezoid, Static	Screw-on Front	No	Aluminum	Anodized

Table 2/3						
Codice a catalogo	Rear Finish	Treated Edges	Rack Height	Altezza (H)	Rack Width	Larghezza (W)
20818-017	Passivated	No	3U	128.4mm	3HP	14.9mm
20818-018	Passivated	No	3U	128.4mm	4HP	20mm
20818-019	Passivated	No	3U	128.4mm	5HP	25mm
20818-020	Passivated	No	3U	128.4mm	6HP	30.1mm
20818-021	Passivated	No	3U	128.4mm	7HP	35.2mm
20818-022	Passivated	No	3U	128.4mm	8HP	40.3mm
20818-023	Passivated	No	3U	128.4mm	10HP	50.5mm
20818-024	Passivated	No	3U	128.4mm	12HP	60.6mm
20818-025	Passivated	No	6U	261.8mm	4HP	20mm
20818-026	Passivated	No	6U	261.8mm	5HP	25mm
20818-027	Passivated	No	6U	261.8mm	6HP	30.1mm
20818-028	Passivated	No	6U	261.8mm	8HP	40.3mm
20818-029	Passivated	No	6U	261.8mm	10HP	50.5mm
20818-120	Passivated	No	6U	261.8mm	12HP	60.6mm

Codice a catalogo	Rear Finish	Treated Edges	Rack Height	Altezza (H)	Rack Width	Larghezza (W)
20818-162	Passivated	No	6U	261.8mm	7HP	35.2mm

Table 3/3				
Codice a catalogo	È conforme a	Indice di infiammabilità	Quantità per confezione	Finitura
20818-017	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20818-018	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20818-019	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20818-020	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20818-021	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20818-022	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20818-023	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20818-024	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20818-025	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20818-026	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20818-027	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20818-028	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20818-029	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20818-120	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated
20818-162	EN 45545-2, R22-R24, HL3, IEC 60297-3-101	UL® 94V-0	1	Anodized, Passivated



AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
 +49.7082.794.0
 Betschdorf, France
 +33.3.88.90.64.90
 Warsaw, Poland
 +48.22.209.98.35
 Assago, Italy
 +39.02.932.7141
 Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:

nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF

TRACER