


## CABLE TO METAL SURFACE, CATHODIC, HB, CAST IRON PIPE OR FLAT SURFACE, #6 CONCENTRIC, 24" MIN PIPE

### CODICE A CATALOGO

## CAHBA1H



nVent ERICO Cadweld Cathodic Connections are the preferred method of exothermically welding cathodic protection anode leads to pipes (steel or cast iron), tanks, and other structures. Cathodic protection systems are designed to prevent galvanic corrosion along a pipeline or in various structures. nVent ERICO Cadweld Cathodic Connections use a special welding material alloy to minimize heat effect on the steel, which is especially important on thin wall and high stress pipes.

### CARATTERISTICHE

Forms a permanent, low resistance connection

Provides a molecular bond

nVent ERICO Cadweld Exothermic Connections are rated with the same current capacity as the conductor

Portable installation equipment with no external source of power required

Installers can be easily trained to make nVent ERICO Cadweld Exothermic Connections

Connections can be visually inspected

### ATTRIBUTI DEL PRODOTTO

Famiglia stampi: HB Mold Family

Si collega a: Cast Iron Pipe or Flat Surface

Dimensioni conduttore: #6 Concentric

Diametro esterno conduttore, nominale: 4.67mm

Dimensione tubo: 24in min

Diametro esterno (OD): 655.3mm min

NB/DN: 600 min

Mold Split: None

Crogiolo diviso: No

Piastre d'usura: No

Solo stampo: No

Materiale per saldatura: CA25XF19 and CA25PLUSXF19, Sold Separately

Handle Clamp: B323N2 and B322, Sold Separately

Telaio: Attached

Chiave prezzi: A

Facilità d'uso: Preferred

## ADDITIONAL PRODUCT DETAILS

For applications such as computer room, tunnel or other low-ventilation areas, specify a smokeless nVent ERICO Cadweld Exolon mold. Add an XL prefix to the standard mold part number when ordering (for example, a TAC2Q2Q becomes XLTAC2Q2Q). Similarly, nVent ERICO Cadweld Exolon welding material is also designated by the XL prefix (for example, 150 becomes XL150).


A test weld should be made to check for the possibility of burn through on thin sections and to determine detrimental metallurgical effects.

Use XF19 or PLUSXF19 welding material on connections to ductile iron.

| W-CA-XX-X-XX-LH-XX-L-M |                      |                                                                                                        |
|------------------------|----------------------|--------------------------------------------------------------------------------------------------------|
| W*                     | Wear Plates          | Reduce mechanical abrasion of molds at cable entry points                                              |
| CA                     | Cathodic Designation |                                                                                                        |
| XX                     | Mold Family          |                                                                                                        |
| X                      | Price Key            |                                                                                                        |
| XX                     | Conductor Size       |                                                                                                        |
| LH                     | Weld End             | LH = Weld on left end of conductor<br>RH = Weld on right end of conductor<br>(For VN Mold Family only) |
| XX                     | Pipe Size            |                                                                                                        |
| L*                     | Split Crucible       | Crucible section is split on molds designed with horizontal opening for easier cleaning                |
| M*                     | Mold Only            |                                                                                                        |

\* Empty if none

## DIAGRAMS



## AVVERTIMENTO

---

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su [www.nvent.com](http://www.nvent.com) e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**