


CABLE TO METAL SURFACE, CATHODIC, VS, STEEL PIPE, 10 MM² CONCENTRIC, 3/4"–3 1/2" PIPE

CODICE A CATALOGO

CAVSTW2A



nVent ERICO Cadweld Cathodic Connections are the preferred method of exothermically welding cathodic protection anode leads to pipes (steel or cast iron), tanks, and other structures. Cathodic protection systems are designed to prevent galvanic corrosion along a pipeline or in various structures. nVent ERICO Cadweld Cathodic Connections use a special welding material alloy to minimize heat effect on the steel, which is especially important on thin wall and high stress pipes.

CARATTERISTICHE

Forms a permanent, low resistance connection

Provides a molecular bond

nVent ERICO Cadweld Exothermic Connections are rated with the same current capacity as the conductor

Portable installation equipment with no external source of power required

Installers can be easily trained to make nVent ERICO Cadweld Exothermic Connections

Connections can be visually inspected

ATTRIBUTI DEL PRODOTTO

Mold Family: VS Mold Family

Connects To: Steel Pipe

Conductor Size: 10 mm² Concentric

Conductor Outer Diameter, Nominal: 4.11mm

Pipe Size: 0.75 – 3.5in

Outer Diameter (OD): 26.7 – 101.6mm

NB/DN: 20 – 90

Mold Split: Vertical

Split Crucible: No

Wear Plates: No

| |
|--|
| Mold Only: No |
| Welding Material: CA15 or CA15PLUSF33, Sold Separately |
| Handle Clamp: Not Required |
| Frame: Not Required |
| Mold Sealer: T403, Sold Separately |
| Price Key: T |
| Ease of Use: Preferred |

ADDITIONAL PRODUCT DETAILS

For applications such as computer room, tunnel or other low-ventilation areas, specify a smokeless nVent ERICO Cadweld Exolon mold. Add an XL prefix to the standard mold part number when ordering (for example, a TAC2Q2Q becomes XLTAC2Q2Q). Similarly, nVent ERICO Cadweld Exolon welding material is also designated by the XL prefix (for example, 150 becomes XL150).

A test weld should be made to check for the possibility of burn through on thin sections and to determine detrimental metallurgical effects.

Use XF19 or PLUSXF19 welding material on connections to ductile iron.

| W-CA-XX-X-XX-LH-XX-L-M | | |
|------------------------|----------------------|--|
| W* | Wear Plates | Reduce mechanical abrasion of molds at cable entry points |
| CA | Cathodic Designation | |
| XX | Mold Family | |
| X | Price Key | |
| XX | Conductor Size | |
| LH | Weld End | LH = Weld on left end of conductor RH = Weld on right end of conductor (For VN Mold Family only) |
| XX | Pipe Size | |
| L* | Split Crucible | Crucible section is split on molds designed with horizontal opening for easier cleaning |
| M* | Mold Only | |

* Empty if none

DIAGRAMS



AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER