

TELECOM MAIN GROUNDING BUSBAR



CERTIFICATIONS



CARATTERISTICHE

Meets TIA-607-C and TIA-607-D and conforms to BICSI® recommendations

Complies with NEMA® standards

Accepts two hole lugs with 5/16" or 7/16" bolt holes (hardware not included)

Telecom grounding busbar splice kits are available to extend the length of the busbar

SPECIFICHE

Spessore (T): 6.35mm
Larghezza (W): 101.6mm
Materiale: Copper


Table 1/2

Codice a catalogo	Lunghezza 1 (L1)	Lunghezza 2 (L2)	Placcatura di stagno	Dimensione del foro 1 Numero di coppie	Dimensione del foro 2 Numero di coppie	C
TMGBA12L15P	305mm	229mm	No	15	3	15.9mm
TMGBA12L15PT	305mm	229mm	Yes	15	3	15.9mm

Codice a catalogo	Lunghezza 1 (L1)	Lunghezza 2 (L2)	Placcatura di stagno	Dimensione del foro 1 Numero di coppie	Dimensione del foro 2 Numero di coppie	C
TMGBA20L27P	508mm	229mm	No	27	3	15.9mm
TMGBA24L33PT	610mm	457mm	Yes	33	5	15.9mm
TMGBA29L41PT	737mm	457mm	Yes	41	5	15.9mm

Table 2/2					
Codice a catalogo	B	A	D	Diametro del foro 1 (HS1)	Diametro del foro 2 (HS2)
TMGBA12L15P	28.6mm	25.4mm	15.9mm	0.3125in	0.4375in
TMGBA12L15PT	28.6mm	25.4mm	15.9mm	0.3125in	0.4375in
TMGBA20L27P	28.6mm	25.4mm	15.9mm	0.3125in	0.4375in
TMGBA24L33PT	28.6mm	25.4mm	15.9mm	0.3125in	0.4375in
TMGBA29L41PT	28.6mm	25.4mm	15.9mm	0.3125in	0.4375in

DIAGRAMS



AVVERTIMENTO

I prodotti nVent devono essere installati e utilizzati solo come indicato nelle schede istruzioni e nei materiali di formazione di nVent. Le schede istruzioni sono disponibili su www.nvent.com e presso il vostro rappresentante del servizio clienti nVent. Un'installazione scorretta, un uso improprio, un'applicazione errata o qualsiasi altro mancato rispetto completo delle istruzioni e degli avvertimenti di nVent può causare malfunzionamenti del prodotto, danni alla proprietà, gravi lesioni personali e morte e/o annullare la vostra garanzia.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER