

TRC FOUR POLE DISTRIBUTION BLOCK, 400 A



CERTIFICATIONS



KENMERKEN

Transparent protection cover

Bolts included for output connections

Easy accessibility for wiring

Ready to use out of the box, saving installation time and labor

RoHS compliant

SPECIFICATIES

Table 1/3

Catalogusnummer	Article Number	Peak Short Circuit Current (I _{pk})	Materiaal	Short Term Withstand Current (I _{cw}) 1s	Line Side Number of Connections	Load Side Number of Connections
TRC-400A	563180	118kA	Copper, Glass Fibre Reinforced Polyamide, Plexiglass	28kA	1	10

Table 2/3

Catalogusnummer	Article Number	Max Working Voltage, IEC (Ui)	Formaat draad 1 (TS1)	Formaat draad 2 (TS2)	Hoogte (H)	Breedte (W)
TRC-400A	563180	1000	M6	M10	338 – 390mm	260mm

Table 3/3


Catalogusnummer	Article Number	Diepte (D)	A	Eenheid gewicht (metrisch)	Flammability Rating	Conform
TRC-400A	563180	50mm	290mm	2.65kg	UL® 94V-0	IEC® 60439.1, IEC® 61439.1, IEC® 60695-2-11 (Glow Wire Test 960 °C)

ADDITIONAL PRODUCT DETAILS

Thread Size 2 represents input plug.

Line side and load side number of connections are per pole.

DIAGRAMS



WAARSCHUWING

nVent-producten moeten alleen worden geïnstalleerd en gebruikt zoals aangegeven in de instructiebladen en trainingsmateriaal van nVent. Instructiebladen zijn beschikbaar op www.nvent.com en bij uw nVent klantenservicevertegenwoordiger. Onjuiste installatie, misbruik, verkeerde toepassing of ander falen om de instructies en waarschuwingen van nVent volledig te volgen, kan leiden tot productstoringen, schade aan eigendommen, ernstig lichamelijk letsel en de dood en/of uw garantie ongeldig maken.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER